

Han 6HP EMC-PFT housing



Part number	19 39 006 1111
Specification	Han 6HP EMC-PFT housing
HARTING eCatalogue	https://b2b.harting.com/19390061111

Identification

Category	Hoods/Housings
Series of hoods/housings Han® HP	
Type of hood/housing	Panel feed through housing
Description of hood/ housing	EMC version

Version

Locking type	Screw locking
Size	6 B
Version	Top entry
Cable gland	1x M25
Field of application	Hoods/housings for rough environments

Technical characteristics

Limiting temperature	-40 +125 °C
Tightening torque (screw locking)	3 Nm
Degree of protection acc. to IEC 60529	IP68 IP69 / IPX9K acc. to ISO 20653

Material properties

Material (hood/housing)	Aluminium die-cast Corrosion resistant
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 9005 (jet black)
RoHS	compliant
ELV status	compliant
China RoHS	е
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No



Material properties

REACH SVHC substances	No

Commercial data

Packaging size	1
Net weight	344 g
Country of origin	China
Customs tariff number	85389099