

PRO380LIGHT

The fully rechargeable PRO380 LIGHT offers a smart select dial, 4x adjustable beam and also acts as a power bank for your USB powered device.

DESIGN

- Fully rechargeable
- Powerbank for your USB powered devices
- 4x adjustable zoom from spotlight to flood light
- Tactical self-defense edge
- Convex lens evenly distributes and focuses the light beam
- Steel belt clip
- Glow-in-the-dark button with battery indicator
- Button doubles as low-profile, stealth light
- Anodized aircraft-grade aluminum; water and impact-resistant
- Anti-roll tactical grip ring
- USB charging in/out port
- Smart Select Dial controls light modes
- Powerful magnetic base



LIGHT MODES

| | |
|--------------------|-----------------------|
| HIGH: 380 Lumens | 4 Hours / 233 Meters |
| MEDIUM: 180 Lumens | 12 Hours / 165 Meters |
| LOW: 38 Lumens | 36 Hours / 74 Meters |
| STEALTH LIGHT | 120 Hours / 1 Meter |
| STROBE: 380 Lumens | 10 Hours / 233 Meters |



Gift Tube Dimensions
(H) 5.5" x (W) 4" x (D) 2.5"

PRO380LIGHT SPECIFICATIONS

| | |
|-------------|--|
| WEIGHT | 0.5 lbs. |
| DIMENSIONS | (L) 6.75" x (W) 1.3125" - Barrel (W) 1.625" - Head |
| BATTERIES | Rechargeable 18650 lithium-ion battery included |
| OPERATION | Rear-positioned glow-in-the-dark ON/OFF button and Smart Select Dial |
| U.S. PATENT | D 659,869 S |

| UPC CODE | ITEM | DESCRIPTION | MSRP |
|--------------|------|--------------------------------------|-------|
| 645397930327 | 6302 | iPROTEC™ PRO380LIGHT with Power Bank | 69.99 |