

NEBO® REDLINE® BLAST



With **1,400 lumens** of high intensity light, this must-have flashlight can throw a spectacularly bright beam over 260 meters. The BLAST is **completely waterproof** (IPX7) and ready for any weather condition. Want more? How about a 4x zoom and 5 light modes (high, medium, low, defensive strobe & flashing beacon).



5 LIGHT MODES

- High (1400 lumens) - 2.5 hours / 260 meters
- Medium (560 lumens) - 7 hours / 180 meters
- Low (140 lumens) - 30 hours / 90 meters
- Strobe (1400 lumens) - 6 hours
- Beacon (200 lumens) - 120 hours



DESIGN

- Convex lens
- Tactical edge
- 4x adjustable zoom
- Signature Red Ring®
- Anodized aircraft-grade aluminum: waterproof (IPX7) and impact-resistant

OPERATION

- Rear-positioned, glow-in-the-dark ON/OFF button with Soft Touch Technology

ACCESSORIES

- Lanyard (Included)

BATTERIES

- Powered by 6 AA batteries (included)

SPECS

- 0.95 lbs.
- Length: Compacted: 7.25" / Extended: 7.75"
- Diameter: (Head) 1.875" / (Barrel) 1.375"

U.S. PATENT

- 659,869 S



Display Dimensions

(H) 12" x (W) 6" x (D) 8.75"

Gift Box Dimensions

(H) 7" x (W) 2" x (D) 1.95"



UPC CODE	ITEM	DESCRIPTION
645397931331	6542	REDLINE® BLAST 1400 Lumen Flashlight

NEBO® REDLINE® RC with MAGDOCK



The REDLINE® RC™ with MagDock features a **MagDock magnetic charging station** that docks and charges your REDLINE®. Small enough to fit in the palm of your hand, the RC™ is fully equipped with all of the features that make the REDLINE® series so popular.

4 LIGHT MODES

- High (320 lumens) - 1 hour / 110 meters
- Medium (125 lumens) - 2 hours / 70 meters
- Low (32 lumens) - 9 hours / 35 meters
- Strobe (320 lumens) - 2 hours / 110 meters

DESIGN

- 4x adjustable zoom
- Anodized aircraft-grade aluminum: water and impact-resistant
- OC™ Technology
- Convex lens
- Signature Red Ring®
- Steel belt/pocket clip
- Magnetic base
- Protective LED housing
- Battery charging indicator

OPERATION

- Side-positioned, ON/OFF button

ACCESSORIES

- USB to Micro USB cable included
- Lanyard included

BATTERIES

- Internal, rechargeable lithium-ion battery (Recharge time - up to 2 hours)

SPECS

- 0.25 lbs.
- Length: Compacted: 3.5625" / Extended: 3.875"
- Diameter: 1.25"

U.S. PATENT

- 8,628,210



OC Technology™ creates a perfectly dispersed beam of intense, pristine light that is as bright on the edge as it is in the center when used in flood mode.

CALIFORNIA REQUIRED ⚠️ WARNING
Cancer and Reproductive Harm
www.P65Warnings.ca.gov/product

UPC CODE	ITEM	DESCRIPTION
645397930754	6392	REDLINE® RC™ with MagDock



Display Dimensions

(H) 11.125" x (W) 5.5" x (D) 7.75"

Gift Box Dimensions

(H) 4.2" x (W) 2.95" x (D) 2.35"