

00 21 19 LB S

KNIPEX L-BOXX® Plumbing 52 parts



- Equipped with 52 brand name quality tools, some VDE tested according to DIN EN 60900
- Several boxes can be securely joined together
- Flexible inner partitions
- With two-part tool holder made of hard-wearing polyester fabric
- Tool holders are connected to each other using hook-and-loop
- Handle can be lowered into a hollow in the lid to save space
- Ergonomically shaped handles with additional moulded recess on the side for flexible, convenient handling
- Dimensions, exterior (W x H x D): 442 x 151 x 357 mm; dimensions, interior (W x H x D): 375 x 107 x 311 mm
- Strong box made of impact- and shock-proof ABS plastic

| | |
|---------------------|---------------|
| Article No. | 00 21 19 LB S |
| EAN | 4003773081630 |
| Net weight g | 9400 |

technical change and errors excepted

L-BOXX® is a registered trademark of Sortimo International GmbH

Content 00 21 19 LB S (25)

| Article No. | | | Quantity | Nominal size | |
|-------------|-----------|---|----------|--------------------------|--|
| 00 11 01 | Knipex | KNIPEX TwinKey®, for all standard cabinets and shut-off systems | 1 | | |
| 26 16 200 | Knipex | Snipe Nose Side Cutting Pliers, (Stork Beak Pliers) | 1 | 200 mm | |
| 74 06 180 | Knipex | High Leverage Diagonal Cutter | 1 | | |
| 86 03 250 | Knipex | Pliers Wrench, pliers and a wrench in a single tool | 1 | | |
| 87 01 250 | Knipex | KNIPEX Cobra®, Hightech Water Pump Pliers | 1 | 250 mm | |
| 87 01 400 | Knipex | KNIPEX Cobra® XL, Pipe Wrench and Water Pump Pliers | 1 | | |
| 98 20 35 | Knipex | Screwdrivers for slotted screws | 1 | 3,5 x 100 mm | |
| 98 20 55 | Knipex | Screwdrivers for slotted screws | 1 | 5,5 mm x 125 mm | |
| 98 26 15 | Knipex | Screwdriver for Torx® screws | 1 | TX15 | |
| 98 26 20 | Knipex | Screwdriver for Torx® screws | 1 | TX20 | |
| 98 26 25 | Knipex | Screwdriver for Torx® screws | 1 | TX25 | |
| 98 24 01 | Knipex | Screwdriver for cross recessed screws, Phillips® | 1 | PH 1 | |
| 98 24 02 | Knipex | Screwdriver for cross recessed screws, Phillips® | 1 | PH 2 | |
| 361 252 1 | Rennsteig | Electrician's Chisel | 1 | 250 x 10 mm | |
| 005655 | Wera | Voltage detector, single-pole, 247 | 1 | 0,5 x 3,0 x 70 mm | |
| 004018 | Wera | 8100 SA 8 Zyklus set of metal ratchets, 28 parts | 1 | 1/4" | |
| 003760 | Wera | Joker open-end wrench | 1 | 10 x 13 mm | |
| 022086 | Wera | set of hex key wrenches | 1 | 1,5 - 10 mm | |
| 90958 | Heyco | Express key | 1 | 17 x 19 mm; M 10 | |
| 16640003 | Heyco | Safety cutter knife | 1 | 18 mm | |
| 101-0300 | Picard | Locksmith's hammer | 1 | 300 g | |
| 340 250 1 | Rennsteig | Mason's Chisels | 1 | 250 mm | |
| 02281 | Stabila | spirit level type 70 | 1 | 30 cm | |
| 71510-000 | Picard | Metre ruler (yardstick) | 1 | 2 m | |
| 6135-0 | Zenten | pipe cutter | 1 | 3 - 35 mm / 1/8 - 1 1/2" | |