

# 13 96 200

## Pliers for Electrical Installation



- 6 functions in one pair of pliers
- Multifunctional pliers for the electrical installation; to grip flat and round material, for bending, deburring, cutting cable, stripping and crimping end sleeves (ferrules)
- Smooth surfaces near the tips grip single cores without damaging them; serrated gripping surfaces and pipe grip for gripping flat and round material
- Clear-cut outside edge on the jaw for working on flush-mounted junction boxes and deburring feed-through holes
- Stripping holes for conductors of 0.75 - 1.5 mm<sup>2</sup> and 2.5 mm<sup>2</sup>
- Crimp die for wire-end ferrules 0.5 - 2.5 mm<sup>2</sup>
- Cable shears with (induction-hardened) precision cutting edges for copper and aluminium cables up to 5 x 2.5 mm<sup>2</sup> / dia. 15 mm
- Gripping, without opening the pliers completely (intelligent latching mechanism in the spring assisted version). The cutting edge remains closed and protected
- Slim dimensions for easy access
- Bolted joint: precise, zero backlash operation of pliers
- In case of models with opening spring integrated in the joint, the activated locking lever keeps the cutting edges closed while other functions remain active
- The intelligent latching mechanism enables you to "grip" without opening the pliers. The cutting edge remains closed and protected.

<b>Article No.</b>	13 96 200
<b>EAN</b>	4003773075110
<b>Head</b>	
<b>Pliers</b>	chrome plated
<b>Handles</b>	insulated with multi-component grips, VDE-tested
<b>Insulation standard</b>	IEC 60900 DIN EN 60900
<b>Cutting capacity copper cable, multiple-stranded (diameter) Ø mm</b>	15
<b>Cutting capacity copper cable, multiple-stranded mm<sup>2</sup></b>	50
<b>Stripping capacity for cross-sections mm<sup>2</sup></b>	0,75 - 1,5 + 2,5
<b>Capacity in square millimetres mm<sup>2</sup></b>	0,5 - 2,5
<b>AWG</b>	1/0
<b>Length mm</b>	200
<b>Net weight g</b>	280



technical change and errors excepted

