

67 01 200

High Leverage End Cutting Nipper



- With cutting edges for soft, hard and piano wire
- High cutting capacity with little effort due to optimum co-ordination of cutting edge angle and transmission ratio
- Cutting edges additionally induction hardened, cutting edge hardness approx. 64 HRC
- Chrome vanadium heavy-duty steel, forged, multi stage oil-hardened



Article No.	67 01 200
EAN	4003773040637
Pliers	black atramentized
Head	polished
Handles	plastic coated
Cutting capacities medium hard wire (diameter) Ø mm	3,8
Cutting capacities hard wire (diameter) Ø mm	3,0
Cutting capacities piano wire (diameter) Ø mm	2,5
Cutting capacities soft wire (diameter) Ø mm	5,0
Length mm	200
Net weight g	318



technical change and errors excepted

