

70 06 125

Diagonal Cutter



- The indispensable diagonal cutter for all-round use
- High-quality material and precise workmanship for long service life
- Precision cutting edges for soft and hard wire
- Clean cutting of thin copper wires, also at the cutting-edge tips
- Cutting edges additionally induction hardened, cutting edge hardness approx. 62 HRC
- Narrow head style for use in confined areas
- Vanadium electric steel, forged, multi stage oil-hardened



Article No.	70 06 125
EAN	4003773018124
Pliers	chrome plated
Handles	insulated with multi-component grips, VDE-tested
Style	0
Head	
Insulation standard	IEC 60900 DIN EN 60900
Cutting capacities medium hard wire (diameter) Ø mm	2,3
Cutting capacities hard wire (diameter) Ø mm	1,5
Cutting capacities soft wire (diameter) Ø mm	3,0
Nominal size	125 mm
Length mm	125
Net weight g	121



Slim head style and precise cut at blade tips: Advantageous when working in confined areas

technical change and errors excepted

