

71 12 200

KNIPEX CoBolt® Compact Bolt Cutters



- Precision cutting edges for soft and hard wire as well as piano wire
- Cuts bolts, nails, rivets, etc. up to 5.2 mm dia.
- Most efficient joint design ensures exceptional cutting performance with little effort
- Cutting edges additionally induction hardened, cutting edge hardness approx. 64 HRC
- Chrome vanadium heavy-duty steel, forged, multi stage oil-hardened
- Improved cutting performance
- Micro-structured cutting edge allows easy cutting of large cross-sections
- With gripping surface below the joint for gripping and pulling wires with a diameter as from 1.0 mm
- With slim multi-component grips without collar for better handling and easier transport
- Opening spring and locking device are integrated in the handles also for comfortable work and protected transport

60 % less effort required compared to conventional high-leverage diagonal cutters

The ingenious lever-action mechanism ensures an extremely favourable lever ratio with very little friction. The cutting force over 30 times higher than the hand force applied.

Article No.	71 12 200	
EAN	4003773066859	
Pliers	black atramentized	
Handles	with slim multi-component grips	
Style	1	
Cutting capacities medium hard wire (diameter) Ø mm	5,2	
Cutting capacities hard wire (diameter) Ø mm	4,0	
Cutting capacities piano wire (diameter) Ø mm	3,6	
Cutting capacities soft wire (diameter) Ø mm	6,0	
Length mm	200	
Net weight g	375	

71 01/02/12 200 and 71 31/32 200

technical change and errors excepted

