86 05 150 Mini Pliers Wrench pliers and a wrench in a single tool







- Replaces the need for sets of metric and imperial spanners
- Smooth jaws for damage free installation of plated fittings working directly on chrome!
- Adjustable tightening tool
- Also excellent for gripping, holding, pressing and bending workpieces
- Push the button for adjustment on the workpiece
- Zero backlash jaw pressure prevents damage to edges of sensitive components
- Parallel jaws give a more solid grip; its design allows flexible adjustment of all widths up to the specified maximum size
- Reliable catching of the hinge bolt: no unintentional shifting
- The ratchet type principle allows quick and easy tightening and release of all bolted connections
- Lever transmission greater than 10 : 1 for strong gripping power
- Chrome vanadium electric steel, forged, oil-hardened
- The mini pliers wrench for precision mechanics
- Ideal multi-purpose wrench in pocket size
- Indispensable companion in emergency tool kit

The smooth jaws grip all parallel surfaces in the capacity range with a high degree of pressure if necessary and open up almost unlimited application possibilities for the pliers wrench: e.g. for tightening locknuts, exerting pressure to activate the adhesive power of contact adhesives, edge breaking in tile work, snapping cable ties, utilisation as a small vice.

Article No.	86 05 150	
EAN	4003773069928	
Pliers	chrome plated	
Handles	with multi-component grips	
B2 mm	7,0	
B3 mm	10,5	
B1 mm	4,7	
Adjustment positions	14	
Capacities for nuts Inch	1	
Capacities for nuts mm	27	5
Length mm	150	
Net weight g	193	



Pliers wrench: zero backlash contact pressure, no damage to edges



Conventional open end wrench: edge pressure causes surface damage

technical change and errors excepted



Spare Parts

Article No.	EAN	
86 09 150	4003773073123	Range of spare parts adjustment for 86 150