

87 26 250 T

KNIPEX Cobra® VDE Hightech Water Pump Pliers, insulated with tether attachment point



- Adjustment by shifting one jaw directly on to the workpiece: fast, reliable and comfortable handling
- Fine adjustment: allows optimum adjustment to differently sized workpieces and comfortable handle position
- Good access to the workpiece
- Self-locking on pipes and nuts: no slipping on the workpiece and low handforce required
- Gripping surfaces with special hardened teeth, teeth hardness approx. 61 HRC: high wear resistance and stable gripping
- Box-joint design for high stability due to double guide
- High load capacity having a slim design
- Guard prevents operators' fingers being pinched
- Chrome vanadium electric steel, forged, multi stage oil-hardened
- Pliers with integrated, insulated tether attachment point for a tool tether

Article No.	87 26 250 T
EAN	4003773081517
Pliers	chrome plated
Handles	insulated with multi-component grips, VDE-tested with integrated insulated tether attachment point for a tool tether
Head	
Insulation standard	IEC 60900 DIN EN 60900
Adjustment positions	24
Capacity for pipes, inches (diameter) Ø Inch	2
Capacities for nuts mm	46
Capacities for pipes (diameter) Ø mm	50
Length mm	250
Net weight g	397

technical change and errors excepted