

95 62 160

Wire Rope Cutter Also for high-strength wire rope



- Compact, light and powerful
- Up to 30 % less physical effort compared to wire rope cutters of the same length
- Double-mounted box joint design for high level of stability
- Cutting edges additionally induction hardened, cutting edge hardness approx. 64 HRC
- Convenient work thanks to opening spring
- Secured by locking device during transport
- Ball bearing steel
- For wire rope with $\varnothing 4.00 / 1960 \text{ Nmm}^2$

Article No.	95 62 160
EAN	4003773082354
Head	
Tool	burnished
Handles	with multi-component grips
Cutting capacity copper cable, multiple-stranded (diameter) Ø mm	6,0
Cutting capacities wire rope (diameter) Ø mm	4,0
Length mm	160
Net weight g	170



Compact at 160 mm but nevertheless more powerful than many larger wire rope cutters



For cutting high-strength wire ropes (1960 N/mm²) with a diameter of up to 4 mm



Double-bearing joint

technical change and errors excepted