

97 52 36

KNIPEX PreciForce® Crimping Pliers



- Repetitive, high crimping quality due to precision dies and integral lock (self-releasing mechanism)
- Crimping pressure has been set precisely (calibrated) in the factory, re-adjustable
- Optimum transmission of force thanks to toggle lever for fatigue-reduced operation
- Good handling thanks to favourable handle position, low weight, compact design and ergonomically shaped handles
- Chrome vanadium electric steel in special quality, oil-hardened



For daily crimping applications, the specialist likes crimping pliers that work precisely and reliably. In addition, they should be light, comfortable to use, robust and reasonably priced: PreciForce®.

Article No.	97 52 36
EAN	4003773051893
Pliers	burnished
Handles	with multi-component grips
Applications	insulated terminals, plug connectors + butt connectors
Capacity in square millimetres mm²	0,5 - 6,0
Number of crimping positions	3
AWG	20 - 10
Length mm	220
Net weight g	487



97 52 36

technical change and errors excepted

