

97 52 64

Four-Mandrel Crimping Pliers for turned contacts



- For crimping turned contacts
- Four-mandrel crimping for top-quality crimping connections
- Mandrel gauge to check the basic setting
- Repetitive, high crimping quality due to integral lock (self-releasing mechanism)
- Optimum transmission of force due to highly effective lever action for fatigue-reduced operation
- High operation comfort thanks to handy shape
- Chrome vanadium electric steel in special quality, oil-hardened
- Pressure adjustment depending on the conductor's diameter by means of adjusting wheel in 4 different positions
- Locator for positioning the contacts



Turned contacts are used for particularly demanding plug-type connections, e.g. in medical industry and aeronautics. Extremely reliable crimping connections can be achieved only with pliers that work with absolute precision and maintain the required crimping depth in the 1/100 mm range.

Article No.	97 52 64
EAN	4003773044093
Pliers	chrome plated
Handles	with multi-component grips
Applications	turned contacts
Capacity in square millimetres mm²	0,08 - 2,5
Number of crimping positions	1
Max. contact diameter mm	5
AWG	28 - 13
Length mm	180
Net weight g	424

technical change and errors excepted



Spare Parts

Article No.	EAN	
97 59 22	4003773053958	Extension spring for 97 52 64