

# 98 20 25

## Screwdrivers for slotted screws



- Ergonomically optimised dual component handle for fatigue reduced work and optimum transmission of force
- Handle design prevents rolling
- Chrome vanadium molybdenum steel



<b>Article No.</b>	98 20 25
<b>EAN</b>	4003773062325
<b>Tip</b>	burnished
<b>Handle</b>	insulating multi-component handle, VDE-tested
<b>Insulation standard</b>	IEC 60900 DIN EN 60900
<b>Blade width mm</b>	2,5
<b>Blade length mm</b>	75
<b>Handle length mm</b>	102
<b>Nominal size</b>	2,5 mm
<b>Blade thickness mm</b>	0,4
<b>Length of non-insulated blade mm</b>	15
<b>Length mm</b>	177
<b>Net weight g</b>	32

*technical change and errors excepted*

