

**18TH
EDITION
COMPLIANT**



SIZING GUIDE

LINIAN 
FIRE CLIP | FASTER. SAFER. SIMPLER.

For more information:
Call **0141 465 4858**

FIREPROOF CABLES

STANDARD FIRE ALARM AND SECURITY WIRING CABLES

Conductor Size	Overall Diameter	LINIAN Clip Part Number (1 Cable)	LINIAN Clip Part Number (2 Cables)
1	7.5	1LCx608	1LCx682
1	8	1LCx608	1LCx682
1	8.8	1LCx608	1LCx682
1	10.5	1LCx911	1LCx9112
1	13.7	1LSCx1214	
1.5	8	1LCx608	1LCx682
1.5	8.4	1LCx608	1LCx682
1.5	9.5	1LCx911	1LCx9112
1.5	11.3	1LCx911	1LCx9112
1.5	15.2	1LSCx1517	
1.5	17.8	1LSCx1517	
2.5	9	1LCx911	1LCx9112
2.5	10.5	1LCx911	1LCx9112
2.5	11.7	1LCx911	1LCx9112
2.5	13.7	1LSCx1214	
2.5	17.9	1LSCx1517	
2.5	21.4	1LSCx2022	
4	11.3	1LCx911	1LCx9112
4	12.1	1LSCx1214	
4	13.3	1LSCx1214	

ENHANCED FIRE ALARM AND SECURITY WIRING CABLES

Conductor Size	Overall Diameter	LINIAN Clip Part Number (1 Cable)	LINIAN Clip Part Number (2 Cables)
1.5	8	1LCx608	1LCx682
1.5	8.4	1LCx608	1LCx682
1.5	9.5	1LCx911	1LCx9112
2.5	9	1LCx911	1LCx9112
2.5	10.5	1LCx911	1LCx9112
2.5	11.7	1LCx911	1LCx9112
4	11.3	1LCx911	1LCx9112
4	12.1	1LSCx1214	
4	13.3	1LSCx1214	

Substitute 'x' in each part number with the preferred colour choice R- Red, W - White or B - Black

FIXED WIRING AND MAINS CABLES PVC

6491X (HO7V-R) PVC

Conductor Size	Overall Diameter	LINIAN Clip Part Number (1 Cable)	LINIAN Clip Part Number (2 Cables)
10	6.15	1LCx608	1LCx682
16	7.1	1LCx608	1LCx682
25	8.9	1LCx608	1LCx682
35	9.95	1LCx911	1LCx9112
50	11.7	1LCx911	1LCx9112
70	13.35	1LSCx1214	
95	15.6	1LSCx1517	
120	17.2	1LSCx1517	
150	19.1	1LSCx1820	
185	21.3	1LSCx2022	
240	24.3	1LSCx2325	
300	27.05	1LSCx2325	

6491B (HO7Z-R) LSZH

Conductor Size	Overall Diameter	LINIAN Clip Part Number (1 Cable)	LINIAN Clip Part Number (2 Cables)
10	6.15	1LCx608	1LCx682
16	7.1	1LCx608	1LCx682
25	8.9	1LCx608	1LCx682
35	9.95	1LCx911	1LCx9112
50	11.7	1LCx911	1LCx9112
70	13.35	1LSCx1214	
95	15.6	1LSCx1517	
120	17.2	1LSCx1517	
150	19.1	1LSCx1820	
185	21.3	1LSCx2022	
240	24.3	1LSCx2325	

FIXED WIRING AND MAINS CABLES PVC

SURFACE WIRING CABLES PVC 6181Y

Conductor Size	Overall Diameter	LINIAN Clip Part Number (1 Cable)	LINIAN Clip Part Number (2 Cables)
2.5	6	1LCx608	1LCx682
4	6.8	1LCx608	1LCx682
6	7.4	1LCx608	1LCx682
10	8.8	1LCx608	1LCx682
16	10.5	1LCx911	1LCx9112
25	12.5	1LSCx1214	
35	13.5	1LSCx1214	
50	14.38	1LSCx1214	
70	15.3	1LSCx1517	
95	17.5	1LSCx1517	
120	19.3	1LSCx1820	

SURFACE WIRING CABLES PVC 624*Y

Conductor Size	Overall Diameter	LINIAN Clip Part Number (1 Cable)	LINIAN Clip Part Number (2 Cables)
1	4.15 x 5.40	1LCx608	1LCx682
1.5	4.55 x 8.8	1LCx608	1LCx682
2.5	5.4 x 10.5	1LCx608	1LCx682
4	6.1 x 12	1LCx608	1LCx682
6	6.9 x 13.8	1LCx608	1LCx682
10	8.4 x 18.5	1LCx608	1LCx682

SURFACE WIRING CABLES LSZH 6181B

Conductor Size	Overall Diameter	LINIAN Clip Part Number (1 Cable)	LINIAN Clip Part Number (2 Cables)
2.5	6	1LCx608	1LCx682
4	6.8	1LCx608	1LCx682
6	7.4	1LCx608	1LCx682
10	8.8	1LCx608	1LCx682
16	10.5	1LCx911	1LCx9112
25	12.5	1LSCx1214	
35	13.5	1LSCx1214	

MAINS AND CONTROL CABLES PVC

Conductor Size	Overall Diameter	LINIAN Clip Part Number (1 Cable)	LINIAN Clip Part Number (2 Cables)
1.5	11.6	1LCx911	1LCx9112
1.5	11.54	1LCx911	1LCx9112
1.5	12.26	1LSCx1214	
1.5	13.3	1LSCx1214	
1.5	14.1	1LSCx1214	
1.5	16.7	1LSCx1517	
1.5	18	1LSCx1820	
1.5	18.3	1LSCx1820	
1.5	20.78	1LSCx1820	
1.5	25.1	1LSCx2325	
2.5	12.4	1LSCx1214	
2.5	12.99	1LSCx1214	
2.5	13.86	1LSCx1214	
2.5	14.92	1LSCx1214	
2.5	15.96	1LSCx1517	
2.5	20	1LSCx2022	
2.5	21.11	1LSCx2022	
2.5	25.16	1LSCx2325	
4	13.38	1LSCx1214	
4	14.05	1LSCx1214	
4	15.04	1LSCx1517	
4	16.35	1LSCx1517	
4	18.21	1LSCx1820	
4	24.24	1LSCx2325	
6	14.38	1LSCx1214	
6	15.14	1LSCx1517	
6	17.03	1LSCx1517	
6	18.39	1LSCx1820	

Substitute 'x' in each part number with the preferred colour choice R- Red, W - White or B - Black

FIXED WIRING AND MAINS CABLES PVC

MAINS AND CONTROL CABLES PVC (continued)

Conductor Size	Overall Diameter	LINIAN Clip Part Number (1 Cable)	LINIAN Clip Part Number (2 Cables)
10	16.18	1LSCx1517	
10	17.76	1LSCx1517	
10	19.09	1LSCx1820	
10	20.91	1LSCx1820	
16	19.06	1LSCx1820	
16	20.35	1LSCx1820	
16	21.95	1LSCx2022	
16	25.19	1LSCx2325	

MAINS CABLES PVC

Conductor Size	Overall Diameter	LINIAN Clip Part Number (1 Cable)	LINIAN Clip Part Number (2 Cables)
25	20	1LSCx2022	
25	23	1LSCx2325	
25	25	1LSCx2325	
35	22	1LSCx2022	
50	26	1LSCx2325	

Substitute 'x' in each part number with the preferred colour choice R- Red, W - White or B - Black



FIXED WIRING AND MAINS CABLES LSZH

MAINS AND CONTROL CABLES LSZH

Conductor Size	Overall Diameter	LINIAN Clip Part Number (1 Cable)	LINIAN Clip Part Number (2 Cables)
1.5	11	1LCx911	1LCx9112
1.5	11.2	1LCx911	1LCx9112
1.5	12.5	1LSCx1214	
1.5	12.9	1LSCx1214	
1.5	13.7	1LSCx1214	
1.5	18	1LSCx1820	
1.5	20.6	1LSCx2022	
1.5	25.1	1LSCx2325	
2.5	12.2	1LSCx1214	
2.5	12.8	1LSCx1214	
2.5	13.5	1LSCx1214	
2.5	14.7	1LSCx1214	
2.5	15.6	1LSCx1517	
2.5	21	1LSCx2022	
2.5	25	1LSCx2325	
4	13.1	1LSCx1214	
4	13.7	1LSCx1214	
4	14.8	1LSCx1214	
4	16.35	1LSCx1517	
4	18.2	1LSCx1820	
4	24.24	1LSCx2325	
4	27.61	1LSCx2325	
6	14.1	1LSCx1214	
6	14.8	1LSCx1214	
6	17.3	1LSCx1517	
6	18.39	1LSCx1820	
6	21.9	1LSCx2022	
10	16.1	1LSCx1517	
10	17.9	1LSCx1517	
10	19.3	1LSCx1820	
10	20.91	1LSCx2022	
10	25	1LSCx2325	
16	19	1LSCx1820	
16	20	1LSCx1820	

FIXED WIRING AND MAINS CABLES LSZH

MAINS AND CONTROL CABLES LSZH (continued)

Conductor Size	Overall Diameter	LINIAN Clip Part Number (1 Cable)	LINIAN Clip Part Number (2 Cables)
16	22	1LSCx2022	
16	25.19	1LSCx2325	

SINGLE CORE NON-ARMOURED MAINS CABLES PVC

Conductor Size	Overall Diameter	LINIAN Clip Part Number (1 Cable)	LINIAN Clip Part Number (2 Cables)
50	13.5	1LSCx1214	
70	15.5	1LSCx1517	
95	17.5	1LSCx1517	
120	19	1LSCx1820	
150	21.5	1LSCx2022	
185	23.5	1LSCx2325	
240	26.5	1LSCx2325	

SCREENED FIXED WIRING AND MAINS CABLES TO BS 8436

Conductor Size	Overall Diameter	LINIAN Clip Part Number (1 Cable)	LINIAN Clip Part Number (2 Cables)
1	8.6	1LCx608	1LCx682
1	9.4	1LCx911	1LCx9112
1	10	1LCx911	1LCx9112
1.5	9.8	1LCx911	1LCx9112
1.5	10.4	1LCx911	1LCx9112
1.5	11.3 ²²	1LCx911	1LCx9112
2.5	10.8	1LCx911	1LCx9112
2.5	11.1	1LCx911	1LCx9112
2.5	12.6	1LSCx1214	
4	11.5	1LCx911	1LCx9112
4	13.1	1LSCx1214	
4	13.9	1LSCx1214	
6	13.1	1LSCx1214	
6	14.2	1LSCx1214	
6	14.9	1LSCx1214	
10	16.1	1LSCx1517	

Substitute 'x' in each part number with the preferred colour choice R- Red, W - White or B - Black

MAINS CABLES LSZH

Conductor Size	Overall Diameter	LINIAN Clip Part Number (1 Cable)	LINIAN Clip Part Number (2 Cables)
25	20	1LSCx1820	
25	23	1LSCx2325	
25	25	1LSCx2325	
35	22	1LSCx2022	
35	26	1LSCx2325	
50	25	1LSCx2325	

SINGLE CORE NON-ARMOURED MAINS CABLES LSZH

Conductor Size	Overall Diameter	LINIAN Clip Part Number (1 Cable)	LINIAN Clip Part Number (2 Cables)
50	13	1LSCx1214	
70	15.5	1LSCx1517	
95	18	1LSCx1820	
120	19.5	1LSCx1820	
150	21.5	1LSCx2022	
185	24	1LSCx2325	

FIXED WIRING AND MAIN CABLES

Conductor Size	Overall Diameter	LINIAN Clip Part Number (1 Cable)	LINIAN Clip Part Number (2 Cables)
50	17.7	1LSCx1517	
70	19.6	1LSCx1820	
95	21.5	1LSCx2022	
120	23.1	1LSCx2325	
150	26	1LSCx2325	

SINGLE CORE ARMOURED MAINS CABLES LSZH

Conductor Size	Overall Diameter	LINIAN Clip Part Number (1 Cable)	LINIAN Clip Part Number (2 Cables)
50	17.7	1LSCx1517	
70	19.6	1LSCx1820	
95	21.5	1LSCx2022	
120	23.1	1LSCx2325	
150	26	1LSCx2325	

FLEXIBLE CABLES

PVC INSULATED FLEXIBLE CORDS 218*Y 318*Y

Conductor Size	Overall Diameter	LINIAN Clip Part Number (1 Cable)	LINIAN Clip Part Number (2 Cables)
0.75	6.1	1LCx608	1LCx682
0.5	6.3	1LCx608	1LCx682
0.75	6.8	1LCx608	1LCx682
0.75	7.2	1LCx608	1LCx682
0.75	7.7	1LCx608	1LCx682
0.75	8.5	1LCx608	1LCx682
1	7.2	1LCx608	1LCx682
1	7.6	1LCx608	1LCx682
1	8.5	1LCx608	1LCx682
1	9.1	1LCx911	1LCx9112
1.5	8.2	1LCx911	1LCx9112
1.5	8.9	1LCx911	1LCx9112
1.5	10	1LCx911	1LCx9112
1.5	11	1LCx911	1LCx9112
2.5	9.9	1LCx911	1LCx9112
2.5	10.8	1LCx911	1LCx9112
2.5	11.3	1LCx911	1LCx9112
2.5	12.8	1LSCx1214	

TRI-RATED EQUIPMENT WIRES

Conductor Size	Overall Diameter	LINIAN Clip Part Number (1 Cable)	LINIAN Clip Part Number (2 Cables)
10	6.3	1LCx608	1LCx682
16	9	1LCx911	1LCx9112
25	10.4	1LCx911	1LCx9112
35	11.9	1LCx911	1LCx9112
50	14.7	1LSCx1214	
70	16.8	1LSCx1518	
95	18.8	1LSCx1820	
120	19.9	1LSCx2022	
150	22.9	1LSCx2022	
185	24.1	1LSCx2325	

ZERO HALOGEN FLEXIBLE CORDS (HO5 ZIFI-F)

Conductor Size	Overall Diameter	LINIAN Clip Part Number (1 Cable)	LINIAN Clip Part Number (2 Cables)
0.75	6.8	1LCx608	1LCx682
0.75	7.2	1LCx608	1LCx682
0.75	7.7	1LCx608	1LCx682
0.75	8.5	1LCx608	1LCx682
1.00	7.2	1LCx608	1LCx682
1.00	7.6	1LCx608	1LCx682
1.00	8.5	1LCx608	1LCx682
1	9.1	1LCx911	1LCx9112
1.5	8.2	1LCx911	1LCx9112
1.5	8.9	1LCx911	1LCx9112
1.5	10	1LCx911	1LCx9112
1.5	11	1LCx911	1LCx9112
2.5	9.9	1LCx911	1LCx9112
2.5	10.8	1LCx911	1LCx9112
1.5	11.3	1LCx911	1LCx9112
2.5	12.8	1LSCx1214	

ARCTIC GRADE FLEXIBLE CORDS

Conductor Size	Overall Diameter	LINIAN Clip Part Number (1 Cable)	LINIAN Clip Part Number (2 Cables)
1.5	8.2	1LCx608	1LCx682
1.5	9.55	1LCx911	1LCx9112
2.5	10.15	1LCx911	1LCx9112
2.5	11.3	1LCx911	1LCx9112
4	11.4	1LCx911	1LCx9112
6	13.2	1LSCx1214	

Substitute 'x' in each part number with the preferred colour choice R- Red, W - White or B - Black

FLEXIBLE CABLES

TYPE YY CONTROL CABLES

Conductor Size	Overall Diameter	LINIAN Clip Part Number (1 Cable)	LINIAN Clip Part Number (2 Cables)
0.75	5.6	1LCx608	1LCx682
0.75	5.7	1LCx608	1LCx682
0.75	6.2	1LCx608	1LCx682
0.75	7	1LCx608	1LCx682
0.75	7.3	1LCx608	1LCx682
0.75	9.5	1LCx911	1LCx9112
0.75	11.1	1LCx911	1LCx9112
0.75	13.2	1LSCx1214	
0.75	16.7	1LSCx1518	
0.75	18.4	1LSCx1820	
0.75	23.5	1LSCx2325	
1	6	1LCx608	1LCx682
1	6.1	1LCx608	1LCx682
1	6.7	1LCx608	1LCx682
1	7.5	1LCx608	1LCx682
1	8.1	1LCx608	1LCx682
1	11	1LCx911	1LCx9112
1	12.7	1LSCx1214	
1	15.5	1LSCx1518	
1	18.3	1LSCx1820	
1	19	1LSCx1820	
1	21.3	1LSCx2022	
1	25.6	1LSCx2325	
1.5	6.6	1LCx608	1LCx682
1.5	7	1LCx608	1LCx682
1.5	7.6	1LCx608	1LCx682
1.5	8.1	1LCx608	1LCx682
1.5	9.2	1LCx911	1LCx9112
1.5	11.2	1LCx911	1LCx9112
1.5	12.4	1LSCx1214	
1.5	13.1	1LSCx1214	
1.5	14.8	1LSCx1214	
1.5	18	1LSCx1820	
1.5	21	1LSCx2022	
1.5	24.2	1LSCx2325	

TYPE YY CONTROL CABLES

Conductor Size	Overall Diameter	LINIAN Clip Part Number (1 Cable)	LINIAN Clip Part Number (2 Cables)
2.5	7.8	1LCx608	1LCx682
2.5	8.1	1LCx608	1LCx682
2.5	8.9	1LCx608	1LCx682
2.5	9.7	1LCx911	1LCx9112
2.5	11.1	1LCx911	1LCx9112
2.5	13.5	1LSCx1214	
2.5	13.8	1LSCx1214	
2.5	17.5	1LSCx1518	
2.5	22	1LSCx2022	
2.5	25.8	1LSCx2325	
4	10.4	1LCx911	1LCx9112
4	10.7	1LCx911	1LCx9112
4	12.4	1LSCx1214	
4	14	1LSCx1214	
6	11.5	1LCx911	1LCx9112
6	12.8	1LSCx1214	
6	14.6	1LSCx1214	
6	15.2	1LSCx1518	
10	15.3	1LSCx1518	
10	16.5	1LSCx1518	
10	18.6	1LSCx1820	
16	18.4	1LSCx1820	
16	19.9	1LSCx1820	
16	22.4	1LSCx2022	
25	21.5	1LSCx2022	
25	22.5	1LSCx2022	

Substitute 'x' in each part number with the preferred colour choice R- Red, W - White or B - Black

FLEXIBLE CABLES

TYPE CY CONTROL CABLES

Conductor Size	Overall Diameter	LINIAN Clip Part Number (1 Cable)	LINIAN Clip Part Number (2 Cables)
0.5	5	1LCx608	1LCx682
0.5	5.2	1LCx608	1LCx682
0.5	6.2	1LCx608	1LCx682
0.5	7	1LCx608	1LCx682
0.5	7.2	1LCx608	1LCx682
0.75	5.5	1LCx608	1LCx682
0.75	5.8	1LCx608	1LCx682
0.75	6.5	1LCx608	1LCx682
0.75	7.1	1LCx608	1LCx682
0.75	7.6	1LCx608	1LCx682
0.75	9.9	1LCx911	1LCx9112
0.75	11.7	1LCx911	1LCx9112
0.75	13.9	1LSCx1214	
1	6.3	1LCx608	1LCx682
1	6.4	1LCx608	1LCx682
1	7.2	1LCx608	1LCx682
1	7.8	1LCx608	1LCx682
1	8.5	1LCx608	1LCx682
1	11.3	1LCx911	1LCx9112
1	13.3	1LSCx1214	
1	16.23	1LSCx1518	
1	19.5	1LSCx1820	
1.5	6.5	1LCx608	1LCx682
1.5	6.9	1LCx608	1LCx682
1.5	7.7	1LCx608	1LCx682
1.5	8.6	1LCx608	1LCx682
1.5	9.2	1LCx911	1LCx9112
1.5	12.7	1LSCx1214	
1.5	14.7	1LSCx1214	
1.5	17.49	1LSCx1518	
1.5	19.89	1LSCx1820	
1.5	23.8	1LSCx2325	
2.5	8	1LCx608	1LCx682
2.5	8.4	1LCx608	1LCx682

TYPE CY CONTROL CABLES (continued)

Conductor Size	Overall Diameter	LINIAN Clip Part Number (1 Cable)	LINIAN Clip Part Number (2 Cables)
2.5	9.19	1LCx911	1LCx9112
2.5	10.3	1LCx911	1LCx9112
2.5	11.2	1LCx911	1LCx9112
2.5	16.8	1LSCx1518	
4	10.5	1LCx911	1LCx9112
4	10.3	1LCx911	1LCx9112
4	11.8	1LCx911	1LCx9112
4	13	1LSCx1214	
6	12.9	1LSCx1214	
10	17.2	1LSCx1518	
16	21	1LSCx2022	

TYPE SY CONTROL CABLES

Conductor Size	Overall Diameter	LINIAN Clip Part Number (1 Cable)	LINIAN Clip Part Number (2 Cables)
4	12.2	1LSCx1214	
4	13.4	1LSCx1214	
4	15	1LSCx1518	
4	16	1LSCx1518	
6	13.4	1LSCx1214	
6	14.6	1LSCx1214	
6	16.7	1LSCx1518	
6	18	1LSCx1820	
10	17.3	1LSCx1518	
10	19.1	1LSCx1820	
10	21	1LSCx2022	
16	20.5	1LSCx1820	
16	22.4	1LSCx2022	
16	25.2	1LSCx2325	

Substitute 'x' in each part number with the preferred colour choice R - Red, W - White or B - Black

FLEXIBLE CABLES

FLEXIBLE MAINS AND CONTROL CABLES HO7RN-F

Conductor Size	Overall Diameter	LINIAN Clip Part Number (1 Cable)	LINIAN Clip Part Number (2 Cables)
1	8	1LCx608	1LCx682
1	8.5	1LCx608	1LCx682
1	9.3	1LCx911	1LCx9112
1.5	9.8	1LCx911	1LCx9112
1.5	10.4	1LCx911	1LCx9112
1.5	11.6	1LCx911	1LCx9112
1.5	11.2 // 14.4	1LCx911 // 1LSCx1214	1LCx9112
1.5	18.2	1LSCx1820	
1.5	22.4	1LSCx2022	
2.5	9.0 // 11.6	1LCx608 // 1LCx911	1LCx682 // 1LCx9112
2.5	9.6 // 12.4	1LCx608 // 1LSCx1214	1LCx682
2.5	10.7 // 13.8	1LCx608 // 1LSCx1214	1LCx682
2.5	17	1LSCx1518	
2.5	21	1LSCx2022	
2.5	26.2	1LSCx2325	
4	15.1	1LSCx1518	
4	16.2	1LSCx1518	
4	17.9	1LSCx1518	
4	19.9	1LSCx1820	
6	16.8	1LSCx1518	
6	18	1LSCx1820	
6	20	1LSCx2022	
6	22.9	1LSCx2022	
10	9.5 // 11.9	1LCx911	1LCx9112
10	22.6	1LSCx2022	
10	24.2	1LSCx2325	
10	26.5	1LSCx2325	
16	13.4	1LSCx1214	
16	25.7	1LSCx2325	
25	15.8	1LSCx1518	
35	17.9	1LSCx1518	
50	20.6	1LSCx2022	

Substitute 'x' in each part number with the preferred colour choice R- Red, W - White or B - Black

TYPE YY CONTROL CABLES LSZH

Conductor Size	Overall Diameter	LINIAN Clip Part Number (1 Cable)	LINIAN Clip Part Number (2 Cables)
0.75	5.6	1LCx608	1LCx682
0.75	5.7	1LCx608	1LCx682
0.75	6.2	1LCx608	1LCx682
0.75	7	1LCx608	1LCx682
1	6	1LCx608	1LCx682
1	6.1	1LCx608	1LCx682
1	6.7	1LCx608	1LCx682
1	7.5	1LCx608	1LCx682
1.5	6.6	1LCx608	1LCx682
1.5	7	1LCx608	1LCx682
1.5	7.6	1LCx608	1LCx682
1.5	8.1	1LCx608	1LCx682
1.5	9.2	1LSCx1214	
1.5	13.1	1LSCx1214	
1.5	14.8	1LSCx1214	
1.5	18	1LSCx1820	
1.5	21	1LSCx2022	
2.5	7.8	1LCx608	1LCx682
2.5	8.1	1LCx608	1LCx682
2.5	8.9	1LCx608	1LCx682
2.5	9.7	1LCx911	1LCx9112
4	10.4	1LCx911	1LCx9112
4	10.7	1LCx911	1LCx9112
4	12.4	1LSCx1214	
6	11.5	1LCx911	1LCx9112
6	12.8	1LSCx1214	
6	14.6	1LSCx1214	
10	15.3	1LSCx1518	
10	16.5	1LSCx1518	
10	18.6	1LSCx1820	
16	18.4	1LSCx1820	
16	19.9	1LSCx1820	
25	21.5	1LSCx2022	

FLEXIBLE CABLES

TYPE SY CONTROL CABLES

Conductor Size	Overall Diameter	LINIAN Clip Part Number (1 Cable)	LINIAN Clip Part Number (2 Cables)
0.75	7.1	1LCx608	1LCx682
0.75	7.6	1LCx608	1LCx682
0.75	8.3	1LCx608	1LCx682
0.75	8.9	1LCx608	1LCx682
0.75	9.5	1LCx911	1LCx9112
0.75	11.9	1LCx911	1LCx9112
0.75	13.2	1LSCx1214	
0.75	13.7	1LSCx1214	
0.75	19	1LSCx1820	
1	7.7	1LCx608	1LCx682
1	8.2	1LCx608	1LCx682
1	9	1LCx911	1LCx9112
1	9.2	1LCx911	1LCx9112
1	10.1	1LCx911	1LCx9112
1	12.9	1LSCx1214	
1	15	1LSCx1518	
1	17.9	1LSCx1518	
1	20	1LSCx1820	
1	23.7	1LSCx2325	
1.5	8.2	1LCx608	1LCx682
1.5	8.6	1LCx608	1LCx682
1.5	9.3	1LCx911	1LCx9112
1.5	10	1LCx911	1LCx9112
1.5	10.7	1LCx911	1LCx9112
1.5	13.8	1LSCx1214	
1.5	16.4	1LSCx1518	
1.5	19.2	1LSCx1820	
1.5	21.6	1LSCx2022	
1.5	23.8	1LSCx2325	
2.5	9.8	1LCx911	1LCx9112
2.5	9.9	1LCx911	1LCx9112
2.5	10.8	1LCx911	1LCx9112
2.5	11.5	1LCx911	1LCx9112
2.5	13	1LSCx1214	

TYPE SY CONTROL CABLES (continued)

Conductor Size	Overall Diameter	LINIAN Clip Part Number (1 Cable)	LINIAN Clip Part Number (2 Cables)
2.5	16.9	1LSCx1518	
2.5	19.8	1LSCx1820	
2.5	23.2	1LSCx2325	
2.5	24.3	1LSCx2325	

FLEXIBLE MAINS AND CONTROL CABLES HO7RN-F

Conductor Size	Overall Diameter	LINIAN Clip Part Number (1 Cable)	LINIAN Clip Part Number (2 Cables)
70	18.6	1LSCx1820	

PVC INSULATED FLEXIBLE CORDS 309*Y

Conductor Size	Overall Diameter	LINIAN Clip Part Number (1 Cable)	LINIAN Clip Part Number (2 Cables)
0.5	6.3	1LCx608	1LCx682
0.5	6.5	1LCx608	1LCx682
0.5	7.2	1LCx608	1LCx682
0.75	6.8	1LCx608	1LCx682
0.75	7.2	1LCx608	1LCx682
0.75	7.7	1LCx608	1LCx682
0.75	8.5	1LCx608	1LCx682
1	7.2	1LCx608	1LCx682
1	7.6	1LCx608	1LCx682
1	8.5	1LCx608	1LCx682
1.5	8.2	1LCx608	1LCx682
1.5	8.9	1LCx608	1LCx682
1.5	10	1LCx911	1LCx9112
2.5	10	1LCx911	1LCx9112
2.5	10.8	1LCx911	1LCx9112
2.5	11.8	1LCx911	1LCx9112

Substitute 'x' in each part number with the preferred colour choice R- Red, W - White or B - Black

CONDUITS AND TRUNKING

CONDUITS

Conduit Size	Conduit Colour	LINIAN Clip Part Number
20mm	White	1LSCW2022
20mm	Black	1LSCB2022
25mm	White	1LSCW2325
25mm	Black	1LSCB2325

MINI TRUNKING

Conduit Size	Conduit Colour
16mm x 10mm	1LCx608 / 1LCx911 / 1LCx682 / 1LCx9112
16mm x 16mm	1LCx608 / 1LCx911 / 1LCx682 / 1LCx9112
25mm x 16mm	1LCx608 / 1LCx911 / 1LCx682 / 1LCx9112
40mm x 16mm	1LCx608 / 1LCx911 / 1LCx682 / 1LCx9112
25mm x 25mm	Complete LINIAN Clip Range
40mm x 25mm	Complete LINIAN Clip Range
50mm x 25mm	Complete LINIAN Clip Range
60mm x 25mm	Complete LINIAN Clip Range
40mm x 40mm	Complete LINIAN Clip Range
60mm x 40mm	Complete LINIAN Clip Range

WWW.LINIANCLIP.CO.UK

