

DC Barrel Jack Adapter – Female

Part No.: LS-00015

Features:

- Barrel jack to bare wires using screw terminal
- 5.5 x 2.1 mm center-positive female barrel jack
- Ideal for connecting power supply with barrel jack to breadboard
- RoHS Compliant

Specifications:

Electrical	
Rated input voltage	14 Volts DC max
Current Rating	1 Amp max
Contact Resistance	30 mΩ max
Insulation resistance	50 mΩ min
Dielectric withstanding voltabe	250V AC for 1 minute
Material	
Temperature Rating	-25 ° C to + 85 ° C
Standard insulator	PBT Glass reinforced, meets UL94V-0