



INDUSTRIAL ETHERNET SWITCHES WITH M12 CONNECTIVITY

Robust unmanaged industrial Ethernet switches with M12 connectivity for use in railways and other forms of public transport. The switches are designed to enable faster and more reliable networks. Depending on the model, the number of ports ranges between five and eight ports, all supporting M12 connectivity. They support data speeds of up to 1 Gb/s, thereby future-proofing against network expansions in the short and medium-term. The switches comply with EN50155, the international standard covering electronics equipment used on rolling stock for railway applications.

BENEFIT STATEMENTS

- M12 cable assemblies support data speed up to 1Gb/s, making the network future proof
- Increases network reliability and safety because of redundant input of power and bypass so that in case of power failure, the switch will transfer data to the next network node
- Save cost by eliminating separate power cables due to optional Power over Ethernet (PoE)
- Compliant with EN50155 to meet international standard covering electronics equipment used in rolling stock for railway applications

Industrial Ethernet Switches with M12 Connectivity

APPLICATIONS

- Public transportation
- Railway
- Tram
- Metro
- Heavy industrial applications

FEATURES

- 5-8 ports supporting M12 connectivity
- Ruggedized switches
- Supports data speeds up to 1Gb/s
- EN50155 compliant
- Optional PoE
- Redundant input power and bypass

STANDARDS & SPECIFICATIONS

- IEEE 802.3 at
- EN50155
- IEC60068-2-27 / -2-32 / -2-6

ELECTRICAL

- Input power 12-57VDC (24VDC) or 71-110VDC
- 5-8 Ethernet ports

MECHANICAL

- IP40
- -40 to 75°C



- Ruggedized M12 Connectivity enables application in Rail
- Optional Bypass improves system reliability
- EN50155 compliant metal casing
- Redundant power supply

Rugged design features	Secure data transmission	Others
<ul style="list-style-type: none"> • M12 Connectors for toughest environments • Shock resistant according to IEC60068-2-27 • Vibration resistant according to IEC60068-2-6 • Reverse polarity protection • Overload current protection 	<ul style="list-style-type: none"> • Compliant to IEEE 802.3 • Dual DC input reduces risk of power failure • Optional bypass function • Relay output enables remote monitoring of the device • Store and forward capabilities 	<ul style="list-style-type: none"> • Operating temp -40 to 75°C • IP-40 • Optional bypass ports help protect the network in case of power failure • Optional POE

Industrial Ethernet Switches with M12 Connectivity

	PN	Description	# ports	# PoE ports	Speed	Input Voltage	Bypass
	500 Mbit/s with POE						
	1-2320401-1	5-PORT 500MBPS SWITCH, 4-PORT POE, 24V	5	4 (max 30W per port)	10/100/500 Base-T(X)	12-57VDC	No
	1-2320401-3	5-PORT 500MBPS SWITCH, 4-PORT POE, MV				72-110VDC	
	1 Gbit/s						
	1-2320402-4	8-PORT 1GBPS SWITCH	8	none	10/100/1000 Base-T(X)	12-48VDC	No
	1-2320402-1	8-PORT 1GBPS SWITCH, 2XBYPASS				72-110VDC	2x
	1-2320402-2	8-PORT 1GBPS SWITCH, MV				72-110VDC	No
	1-2320402-3	8-PORT 1GBPS SWITCH, 2XBYPASS, MV				72-110VDC	2x
	500M/1Gbit/s with POE						
	1-2320404-4	8-PORT 500M/1GBPS POE SWITCH, 24V	8	8	10/100/500/1000 Base-T(X)	12-57VDC	No
	1-2320404-1	8-PORT 500M/1GBPS POE SWITCH, 2XBYPASS, 24V				72-110VDC	2x
	1-2320404-5	8-PORT 500M/1GBPS POE SWITCH, MV				72-110VDC	No
	1-2320404-6	8-PORT 500M/1GBPS POE SWITCH, 2XBYPASS, MV				72-110VDC	2x

te.com

© 2018 TE Connectivity. All Rights Reserved.

TE Connectivity, TE Connectivity (logo) and Every Connection Counts are trademarks. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

While TE has made every reasonable effort to ensure the accuracy of the information in this brochure, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. The dimensions in this catalog are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice. Consult TE for the latest dimensions and design specifications.

1-1773955-7 09/18 Tangence