



NMX All Metal Consumer Units



NMXRS12SSLHI

HIGH INTEGRITY - WITH KNOCKOUTS ALL SIDES

CAT REF	MS RATING	MS WAYS	RCD WAYS	RCD WAYS	TOTAL WAYS	KNOCKOUTS
NMXRS12SSLHI	100A	1 - 6	6 - 1	6 - 1	12	All sides
NMXRS16SSLHI*	100A	1 - 8	8 - 1	8 - 1	16	All sides

HIGH INTEGRITY - PLAIN SIDES

CAT REF	MS RATING	MS WAYS	RCD WAYS	RCD WAYS	TOTAL WAYS	KNOCKOUTS
NMXRS12SSLHIP	100A	1 - 6	6 - 1	6 - 1	12	Rear only (plain sides)
NMXRS16SSLHIP*	100A	1 - 8	8 - 1	8 - 1	16	Rear only (plain sides)

NMX ACCESSORIES

CAT REF	PRODUCT	MODULE
NMXDR2	DIN Rail Insert	2
NMXBB2I	Comb Busbar	21
NMXLDK	Temporary Door Locking Device	-

PATTRESSES

CAT REF	PRODUCT
NMXPAT1618	18 Module Pattress
NMXPAT1622	22 Module Pattress

* Product available 2018



NMXISS12

DUAL RCD - WITH KNOCKOUTS ALL SIDES

CAT REF	MS RATING	MS WAYS	RCD WAYS	RCD WAYS	TOTAL WAYS	KNOCKOUTS
NMXISS12	100A	-	2 - 6	6 - 2	12	All sides
NMXISS16*	100A	-	2 - 8	8 - 2	16	All sides

DUAL RCD - PLAIN SIDES

CAT REF	MS RATING	MS WAYS	RCD WAYS	RCD WAYS	TOTAL WAYS	KNOCKOUTS
NMXISS12P	100A	-	2 - 6	6 - 2	12	Rear only (plain sides)
NMXISS16P*	100A	-	2 - 8	8 - 2	16	Rear only (plain sides)

NMX ACCESSORIES

CAT REF	PRODUCT	MODULE
NMXDR2	DIN Rail Insert	2
NMXBB2I	Comb Busbar	21
NMXLDK	Temporary Door Locking Device	-

PATTRESSES

CAT REF	PRODUCT
NMXPAT1618	18 Module Pattress
NMXPAT1622	22 Module Pattress

* Product available 2018