



Clear Breadboard with 300 Tie Points plus 200 Strip Tie Points



- Solderless square tie points accept wire 20~29AWG
- Spring-clip socket connections
- Built-in buckles connect multiple boards together
- Board thickness: 8.35mm
- Pitch: 2.54mm
- Sturdy ABS board
- Operating temperature: -4°~176°F
- ROHS compliant
- Half-board length
- One terminal strip, two distribution strips
- 300/100 tie points

Length:	4.75 in.
Width:	3 in.
Height:	0.5 in.