

Han 10B HTE M25 PFT CL



Part number	19 30 010 1141
Specification	Han 10B HTE M25 PFT CL
HARTING eCatalogue	https://b2b.harting.com/19300101141

Identification

Category	Hoods/Housings
Series of hoods/housings	Han [®] B
Type of hood/housing	Panel feed through housing
Type	High construction

Version

Locking type	Central locking lever (on the hood)
Size	10 B
Version	Top entry
Cable entry	1x M25
Field of application	Standard hoods/housings for industrial connectors

Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP65

Material properties

Material (hood/housing)	Aluminium die-cast
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 7037 (dust grey)
Material (seal)	NBR

Commercial data

Packaging size	1
Net weight	303 g
Country of origin	China
Customs tariff number	8538900000