

# Han 24B HTE M32 PFT DL



Part number	19 30 024 1121
Specification	Han 24B HTE M32 PFT DL
HARTING eCatalogue	https://b2b.harting.com/19300241121

## Identification

Category	Hoods/Housings
Series of hoods/housings Han® B	
Type of hood/housing	Panel feed through housing
Туре	High construction

# Version

Locking type	Double locking lever
Han-Easy Lock <sup>®</sup>	Yes
Size	24 B
Version	Top entry
Cable entry	1x M32
Field of application	Standard hoods/housings for industrial connectors

# Technical characteristics

Limiting temperature	-40 +125 °C
Degree of protection acc. to IEC 60529	IP65

## Material properties

Material (hood/housing)	Aluminium die-cast
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 7037 (dust grey)
Material (seal)	NBR
Material (locking)	Polycarbonate
	Stainless steel
Colour (locking)	RAL 7037 (dust grey)
Material flammability class acc. to UL 94 (locking levers)	V-0

#### Commercial data

Packaging size 1	
------------------	--

Product data sheet 19 30 024 1121 Han 24B HTE M32 PFT DL



## Commercial data

Net weight	394 g
Country of origin	China
Customs tariff number	8538900000