

Han 16HP Direct cover device side



Part number	09 39 016 5410
Specification	Han 16HP Direct cover device side
HARTING eCatalogue	https://b2b.harting.com/09390165410

Identification

Category	Hoods/Housings
Series of hoods/housings Han® HP Direct B	
Type of hood/housing	Protection cover
Description of hood/ housing	for device side
	With fixing cord

Version

Locking type	Screw locking
Size	16 B

Technical characteristics

Limiting temperature	-40 +120 °C
Tightening torque (screw locking)	4 Nm
Degree of protection acc. to IEC 60529	IP66

Material properties

Material (hood/housing)	Polycarbonate
Colour (hood/housing)	RAL 7037 (dust grey)
Material (seal)	NBR
Material (locking)	Stainless steel
RoHS	compliant with exemption
RoHS exemptions	6c: Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	Yes
REACH SVHC substances	Lead



Specifications and approvals

Specifications	EN 60664-1
	IEC 61984

Commercial data

Packaging size	1
Net weight	89 g
Country of origin	China
Customs tariff number	85389099