

# Han 6HP Direct cover device side



Part number	09 39 006 5410
Specification	Han 6HP Direct cover device side
HARTING eCatalogue	https://b2b.harting.com/09390065410

## Identification

Category	Hoods/Housings
Series of hoods/housings Han® HP Direct B	
Type of hood/housing	Protection cover
Description of hood/	for device side
housing	With fixing cord

## Version

Locking type	Screw locking
Size	6 B

## Technical characteristics

Limiting temperature	-40 +120 °C
Tightening torque (screw locking)	4 Nm
Degree of protection acc. to IEC 60529	IP66

# Material properties

Material (hood/housing)	Polycarbonate
Colour (hood/housing)	RAL 7037 (dust grey)
Material (seal)	NBR
Material (locking)	Stainless steel

# Specifications and approvals

Specifications	EN 60664-1
	IEC 61984

## Commercial data

Packaging size	1
Net weight	71.25 g
Country of origin	China

Product data sheet 09 39 006 5410 Han 6HP Direct cover device side



# Commercial data

Customs tariff number 8538900000