

# Han M23 P fem.-c 0,6mm (0,08-0,34mm<sup>2</sup>) Au



Part number	09 15 600 6291
Specification	Han M23 P femc 0,6mm (0,08– 0,34mm²) Au
HARTING eCatalogue	https://b2b.harting.com/09156006291

# Identification

Category	Contacts
Series	Han <sup>®</sup> M23 Power
Type of contact	Crimp contact
Description of the conta	Turned ct 0.6 mm

#### Version

|--|

#### Technical characteristics

Conductor cross-section	0.08 0.34 mm²
Contact resistance	≤3 mΩ
Stripping length	4 mm

# Material properties

Material (contacts)	Copper alloy
Surface (contacts)	Gold plated

# Specifications and approvals

Specifications	EN 60664-1
	IEC 61984

# Commercial data

Packaging size	100
Net weight	0.19 g
Country of origin	Switzerland
Customs tariff number	85366990