

ASUS VivoBook X540LA-DM1052T(X540LA-DM1052T)
ASUS VivoBook X540LA-DM1052T - Core i3 5005U / 2 GHz - Win 10 Home 64-bit - 4 GB RAM - 1 TB
HDD - 15.6" 1920 x 1080 (Full HD) - HD Graphics 5500 - gold,chocolate black



The ASUS X540 Series is powered by a powerful processor to give you smooth and responsive computing performance. It is an ideal daily computing platform.

Key Selling Points

- Faster and easier connections with USB Type-C
- Expansive audio,tuned by experts
- Crafted speaker design for greater sound
- Lightweight design
- Enjoy a world of color with ASUS Splendid Technology
- Protect your eyes with ASUS Eye Care
- Ergonomic keyboard design
- Stays cool,even after hours of use

Product Features

- Faster and easier connections with USB Type-C
The reversible USB Type-C port makes connecting devices much easier,and gives you super-fast USB 3.1 Gen 1 speeds of up to 5 Gbit/s so you can transfer a 2GB movie to a USB drive in less than 2 seconds! Its compact port design even helps preserve X540's thin dimensions. X540 still carries the traditional USB 3.0 and USB 2.0 ports to ensure compatibility with all your USB devices. X540 has additional connectivity options including HDMI and VGA output for external displays,a 3-in-1 SD/SDHC/SDXC card reader,an RJ-45 Ethernet port,and a DVD Super Multi optical disc drive.
- Expansive audio,tuned by experts
A mixture of hardware,software,and tuning,SonicMaster was developed with the clear goal of giving you the best notebook PC audio. A professional codec ensures precise sound performance;while an optimized amplifier,larger speakers and resonance chambers deliver powerful audio output and deeper bass. Additional signal processing helps fine tune the hardware,filtering noise and improving clarity so you can enjoy unrivaled audio on your X Series.
- Crafted speaker design for greater sound
X540 features round speakers that maximize every cubic millimeter of available chassis space to give you better low frequency performance and reduced noise. The extra-large 19.4cc chamber provides superior bass and excellent sound clarity.
- Lightweight design
ASUS X540 has a solid and lightweight chassis - ideal to take with you when you're out and about. Its premium brushed finish turns heads and makes sure that you stand out from the crowd.
- Enjoy a world of color with ASUS Splendid Technology
To ensure only the very best images,ASUS Splendid Technology has color temperature correction to reproduce richer,deeper colors. It features four visuals modes which can be accessed with a single click. Vivid Mode optimizes contrast for browsing photos or watching videos and movies;Eye Care Mode reduces blue light levels and is ideal when you're reading for long hours. Normal Mode has been tuned for daily tasks;while Manual Mode is for advanced color adjustments.
- Protect your eyes with ASUS Eye Care
Most LED panels emit blue light - the main cause of macular degeneration and retinal problems. ASUS Eye Care mode effectively reduces blue light levels by up to 33% to make reading comfortable,and to protect you from potential eye fatigue and other ailments.
- Ergonomic keyboard design
Typing is now more comfortable than ever with the X Series'full-size one-piece chiclet keyboard. An improved back assembly provides 1.8 mm of key travel and minimal key float,so you get a more solid typing feel.
- Stays cool,even after hours of use
ASUS IceCool Technology gives X Series a unique internal design that addresses uncomfortable heating issues by preventing heat build-up under the palm rest. This keeps the palm rest surface between 28°C to 35°C - significantly lower than body temperature. This exclusive internal layout places heat producing components away from you,and when combined with exceptional cooling from the heat pipes and vents,ensures you stay comfortable even after long hours of use.

Main Specifications

Product Description	ASUS VivoBook X540LA-DM1052T - 15.6" - Core i3 5005U - 4 GB RAM - 1 TB HDD
---------------------	--

Product Type	Notebook
Operating System	Win 10 Home 64-bit
Processor	Intel Core i3 (5th Gen) 5005U / 2 GHz / 3 MB Cache
Memory	4 GB DDR3L (provided memory is soldered)
Storage	1 TB HDD / 5400 rpm
Optical Drive	No optical drive
Display	15.6"LED backlight 1920 x 1080 / Full HD - matte
Graphics	Intel HD Graphics 5500
Numeric Keypad	Yes
Integrated Webcam	Yes
Networking	802.11b/g/n,Bluetooth 4.0,10/100 Ethernet
Battery	3-cell
Colour	Gold,chocolate black
Dimensions (WxDxH)	38.14 cm x 25.15 cm x 2.72 cm
Weight	1.9 kg

Extended Specification

General	
Product Type	Notebook
Operating System	Windows 10 Home 64-bit Edition
Processor / Chipset	
CPU	Intel Core i3 (5th Gen) 5005U / 2 GHz
Number of Cores	Dual-Core
Cache	3 MB
64-bit Computing	Yes
Memory	
RAM	4 GB (provided memory is soldered)
Technology	DDR3L SDRAM
Speed	1600 MHz - 1600 MHz
Storage	
Main Storage	1 TB HDD SATA / 5400 rpm
Display	
Type	15.6"
LCD Backlight Technology	LED backlight
Resolution	1920 x 1080 (Full HD)
Widescreen	Yes
Features	ASUS Splendid Video Intelligence Technology,matte
Audio &Video	
Graphics Processor	Intel HD Graphics 5500

Camera	Yes - VGA
Sound	Stereo speakers,microphone
Audio Features	ASUS SonicMaster,ASUS AudioWizard

Input

Type	Keyboard,touchpad
Numeric Keypad	Yes
Features	ASUS Smart Gesture technology

Communications

Wireless	802.11b/g/n,Bluetooth 4.0
Network Interface	10/100 Ethernet

Battery

Technology	3-cell
Capacity	33 Wh

AC Adapter

Input	AC 120/230 V (50/60 Hz)
Output	45 Watt,19 V,2.47 A

Connections &Expansion

Interfaces	Headphone/microphone combo jack USB 3.1 Gen 1 VGA USB 2.0 HDMI LAN USB-C 3.1 Gen 1
Memory Card Reader	3 in 1 (SD Card,SDHC Card,SDXC Card)

Miscellaneous

Colour	Gold,chocolate black
Features	System password,hard drive password,ASUS IceCool design
Theft/Intrusion Protection	Security lock slot (cable lock sold separately)
Security Slot Type	Kensington security slot
Included Accessories	Power adapter

Dimensions &Weight

Dimensions (WxDxH)	38.14 cm x 25.15 cm x 2.72 cm
Weight	1.9 kg

Product data is provided by CNET,we do not warrant the accuracy and completeness of the material contained in this data sheet