

Part Details:-

Part Number	Description
MKV250V-KIT-1-DE	X/Y/COUPLING CAPACITOR ASSORTMENT KIT

KIT Contents:-

No	Murata P/N	Size (mm/inch)	TC Code	Rated Voltage	Cap.	Tol.	Thickness (mm)	Remarks	Qty
1	GA355QR7GB103KW01	5750M/2220	X7R	AC250V	0.01 μ F	\pm 10%	1.5max		10
2	GA355QR7GB153KW01	5750M/2220	X7R	AC250V	0.015 μ F	\pm 10%	1.5max		10
3	GA355DR7GB223KW01	5750M/2220	X7R	AC250V	0.022 μ F	\pm 10%	2.0max		10
4	GA355ER7GB333KW01	5750M/2220	X7R	AC250V	0.033 μ F	\pm 10%	2.5max		10
5	GA355ER7GB473KW01	5750M/2220	X7R	AC250V	0.047 μ F	\pm 10%	2.5max		10
6	GA355XR7GB563KW06	5750M/2220	X7R	AC250V	0.056 μ F	\pm 10%	2.9max		10
7	GA352QR7GF102KW01	5728M/2211	X7R	AC250V	1000pF	\pm 10%	1.5max		10
8	GA352QR7GF152KW01	5728M/2211	X7R	AC250V	1500pF	\pm 10%	1.5max		10
9	GA355QR7GF222KW01	5750M/2220	X7R	AC250V	2200pF	\pm 10%	1.5max		10
10	GA355QR7GF332KW01	5750M/2220	X7R	AC250V	3300pF	\pm 10%	1.5max		10
11	GA355DR7GF472KW01	5750M/2220	X7R	AC250V	4700pF	\pm 10%	2max		10
12	DE1E3KX102MA4BN01	-	E	AC250V	1000pF	\pm 0.1pF	-		10
13	DE1E3KX152MA4BN01	-	E	AC250V	1500pF	\pm 0.1pF	-		10
14	DE1E3KX222MA4BN01	-	E	AC250V	2200pF	\pm 0.1pF	-		10
15	DE1E3KX332MA4BN01	-	E	AC250V	3300pF	\pm 0.1pF	-		10
16	DE1E3KX472MA4BN01	-	E	AC250V	4700pF	\pm 0.1pF	-		10