



## Smart USB LCD Monitor DS-70U



### Multiple Monitor Solution

Multiple Monitors are a productivity solution and adding a second or third monitor to your computer has never been easier. Simply connect our Smart USB Monitor via a USBPort and run the installation software. That is it. The DoubleSight DS-70U utilizes USB for both power and video. No additional video port, video cable or power adapter required. The DS-70U ships with an adjustable stand for a custom view, including both Landscape and Portrait viewing modes.

### Features include:

- Supports Multi Monitor Mode
- Perfect for Laptops and Desktops
- Lightweight and Portable
- Landscape and Portrait viewing
- USB for Power and Video (no video card required)
- PC and MAC Compatible
- Supports a variety of Applications

### Perfect for:

- Exporting Tool Bars and Menus
- Monitoring Email and viewing Calendars
- Instant Messenger or Internet Phone Applications
- Watch Movies and Internet Video
- View PC based Photo Albums

### Laptop Users

DoubleSight's new Smart USB Monitors are the perfect Laptop accessory. Easily expand your viewable workspace where ever you are. The DS-70U weighs less than one pound and conveniently tucks into your briefcase to go with you. The adjustable stand removes quickly and the snap on cover protects your screen when traveling. A convenient easel stand is tucking into the back of the Monitor to use when traveling.

### Netbook Users

Double the amount of visible work space and increase your productivity, at home or on the road. The DS-70U does not require an extra video port and drivers are easy to download from our web site. Expanding your view has never been easier.

### Desktop Users

Perfect for increasing your viewable desktop where space is tight. Since an additional video port is not required, our USB Monitors are perfect as a second or even a third monitors. DoubleSight's Display Link Software will allow you to connect up to six Smart USB Monitors to your existing PC.

## Display

Panel Type	: LCD
Viewable Area	: 7"
Max. Visible Angle	: 65/65/35/55
Display Colors	: 16.7M
Response Time	: 30ms
Brightness	: 375cd/m
Aspect Ratio	: 16:10
Contrast Ratio	: 350:1
Recommended Resolution	: 800 x 480

## Video Signal

Horizontal Frequency	: USB 2.0 High Speed, No Video Card Required
Vertical Frequency	: USB Mini 5 -pin B Type

## Input/Interface

Interface	: USB for Signal and Power
Input Type	: USB Mini 5 -pin B Type

## Power

AC	: USB for Signal and Power
Power Consumption	: 3.3 ~ 4.9W

## Environment

Operating Temperature	: 32°F - 104°F
-----------------------	----------------

## System

O/S	: Drivers available for Windows, Mac OS, Android and Linux Ubuntu - see download section below for most current drivers
-----	---

## Monitor Characteristics

USB	: Input
Color	: Black
Product Dimensions	: 7" W x 4.75 H x 1" deep (monitor only); 7" W x 8" H x 4" deep (including stand)
Product Weight	: 1 lbs
Certifications	: TAA Compliant
Warranty	: 3 year

## Monitor Stand Adjustments

Adjustable Monitor Stand	: Adjustable - Height, Tilt, Pivot; removable for portability
Height	: yes
Tilt	: yes
Pivot	: yes
Notes	: The Monitor Stand is removable and is interchangeable with the provided Easel Stand.