

12X ADJUSTABLE ZOOM FLASHLIGHT & LANTERN

TACSLYDE™

The TAC SLYDE features a 300 lumen flashlight with 12x adjustable zoom and 5 light modes and a C•O•B lantern feature with 3 light modes, including emergency red flash. A powerful magnetic base provides convenient hands-free lighting, and the lanyard helps keep this light handy when you need it most.

5 FLASHLIGHT MODES

- High (300 lumens) - 2.5 hours / 135 meters
- Medium (150 lumens) - 6 hours / 84 meters
- Low (30 lumens) - 22 hours / 40 meters
- Strobe (300 lumens) - 6 hours / 135 meters
- S.O.S. (300 lumens) - 48 hours / 135 meters

3 LANTERN MODES

- High (200 lumens) - 3 hours / 19 meters
- Low (100 lumens) - 6 hours / 13 meters
- Red Flash (20 lumens) - 8 hours / 6 meters



- Tactical edge
- 12x adjustable zoom
- Anodized aircraft-grade aluminum
- Impact and water-resistant (IPX4)
- Powerful magnetic base
- Rear-positioned, ON/OFF button
- Lanyard included
- Powered by 3 AAA batteries (inc.)
- 0.36 lbs.

TACSLYDE

ITEM #.....6746
UPC.....645397932871
CASE PACK.....18 PIECES



Display showcases 2 pieces, additional pieces included as replenishments.

Display size: (H) 11.75" x (W) 7.25" x (D) 7.875"
Gift box size: (H) 6.02" x (W) 1.5" x (D) 1.5"