




Soldering Irons, Corded Electric

	Model No.	Wattage	Description	Available Tips
 <p>Q Large View</p>	J-012	12	12 Watt Miniature Corded Soldering Iron. UL & C UL approved. Temperature equivalent to standard 25W soldering iron. Tip temperature +680°F (+360°C). Handy in-line ON/OFF switch. Includes safety stand, soldering iron and conical needle tip.	JT-011
 <p>Q Large View</p> <p><i>New Item!</i></p>	J-015E	15	15 Watt Ergonomic Corded Soldering Iron. UL & C UL approved. Heats up to +365°F (+185°C) in 50 seconds. 15 Watts develops +752°F (+400°C) tip temperature. Bent curved handle for comfortable grip. Includes safety stand, soldering iron and conical needle tip.	JT-014
 <p>Q Large View</p>	J-020	20	20 Watt Miniature Corded Soldering Iron. UL & C UL approved. Temperature equivalent to standard 45W soldering iron. Tip temperature +950°F (+510°C). Handy in-line ON/OFF switch. Includes safety stand, soldering iron and conical needle tip.	JT-011
 <p>Q Large View</p>	J-025	25	25 Watt Corded Soldering Iron. UL & C UL approved. Tip temperature +464°F (+240°C). Includes soldering iron and conical needle tip (nickel plated copper).	JT-101
 <p>Q Large View</p> <p><i>New Item!</i></p>	J-025E	25	25 Watt Ergonomic Corded Soldering Iron. UL & C UL approved. Heats up to +365°F (+185°C) in 30 seconds. 25 Watts develops +932°F (+500°C) tip temperature. Bent curved handle for comfortable grip. Includes safety stand, soldering iron and conical needle tip.	JT-014