

Standard cable ties - Jar

All-plastic cable ties

50

Characteristics

- Ty-Fast® cable ties packed in an attractive plastic jar
- Ideal product for the distribution market
- Different dimensions in the same packaging: 112 mm x 2.4 mm, 141 mm x 3.6 mm and 186 mm x 4.7 mm
- Tensile strength from 80N to 220N
- Available in 3 different packaging configurations: 1 in natural cable ties and 2 in black cable ties
- Ideal product when small volumes are needed for various applications

Technical Information

Material	Polyamide 6.6
Temperature range	-40°C to +85°C
Colour	Natural or UV-resistant black (see table)
Flammability rating	UL 94 V-2
Other properties	UV-resistant (black) Halogen free, Silicone free



Product Ref.	Quantity [pieces]	Colour	Mil Spec	Length L [mm]	Width W [N]	Label dimensions [mm]	Quantity [pieces]	Tooling
JTN-500-EU	2 x 100	natural	-	112	2.4	1.6 - 25	80	
	1 x 100	natural	MS-3367-5	141	3.6	1.6 - 32	180	ERG50, WT193A
	2 x 100	natural	MS-3367-1	186	4.6	1.6 - 44	220	ERG50, ERG120, WT193A
JTB-500-EU	2 x 100	UV-resistant black	-	112	2.4	1.6 - 25	80	
	1 x 100	UV-resistant black	MS-3367-5	141	3.6	1.6 - 32	180	ERG50, WT193A
	2 x 100	UV-resistant black	MS-3367-1	186	4.6	1.6 - 44	220	ERG50, ERG120, WT193A
JTB1-500-EU	2 x 100	UV-resistant black	-	112	2.4	1.6 - 25	80	
	2 x 100	UV-resistant black	MS-3367-5	141	3.6	1.6 - 32	180	ERG50, WT193A
	1 x 100	UV-resistant black	MS-3367-1	186	4.6	1.6 - 44	220	ERG50, ERG120, WT193A

Description of Product Reference structure: see page 48

Description of materials and properties: see pages 142 to 153

For tooling specifications: see pages 128 to 141

