

PRODUCT DATASHEET

P PIN 30 2.6 W/4000 K G9

PARATHOM LED PIN G9 | Special LED lamps



AREAS OF APPLICATION

- Atmospheric accent lighting throughout the home
- Shops, hotels and restaurants
- Foyers, offices
- Outdoor applications only in suitable luminaires

PRODUCT BENEFITS

- Long lifetime of up to 15,000 h
- Very low energy consumption
- Ideal for decorative and free-burning applications

PRODUCT FEATURES

- LED alternative to conventional high voltage lamps
- Mercury-free lamps



TECHNICAL DATA

Electrical data

Rated wattage	2.60 W
Nominal wattage	2.60 W
Nominal voltage	220...240 V
Operating frequency	50...60 Hz
Power factor λ	0.40
Claimed equiv. conventional lamp power	30 W


Photometrical data

Nominal luminous flux	320 lm
Rated luminous flux	320 lm
Rated color temperature	4000 K
Lumen main.fact.at end of nom.life time	0.70
Light color (designation)	Cool White
Color temperature	4000 K
Luminous flux	320 lm
Color rendering index Ra	≥ 80
Standard deviation of color matching	≤ 6 sdc _m
Color rendering index Ra	≥ 80

Light technical data

Warm-up time (60 %)	< 0.50 s
Starting time	< 0.5 s

Dimensions & weight



Overall length	52.0 mm
Diameter	15.0 mm
Outer bulb	T15

Length	52.0 mm
---------------	---------

Temperatures & operating conditions

Maximum temperature at tc test point	88 °C
---	-------

Lifespan

Nominal lamp life time	15000 h
Rated lamp life time	15000 h
Number of switching cycles	100000
Lumen maintenance at end of service life	0.70

Additional product data

Base (standard designation)	G9
Mercury content	0.0 mg
Mercury-free	Yes
Design / version	Clear
Show WEEE picto	Yes

Capabilities

Dimmable	No
-----------------	----

Certificates & standards

Energy efficiency class	A++
Energy efficiency class	A++
Energy consumption	3 kWh/1000h

Country-specific categorizations

ILCOS	DRT/C-2,6/840-220-240-G9-15/52
Order reference	LEDPPIN30 CL 2,

LOGISTICAL DATA

Product code	Product description	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Volume	Gross weight
4058075812697	P PIN 30 2.6 W/4000 K G9	Shipping carton box 20	150 mm x 122 mm x 77 mm	1.41 dm ³	223.00 g

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

REFERENCES / LINKS

For further products and actual information concerning LED lamps see

▶ www.ledvance.com/ledlamps

For Guarantee see

▶ www.ledvance.com/guarantee

DISCLAIMER

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.