

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0015921068
Status: Active
Overview: EBBI 50D Connector System
Description: 1.27mm Pitch EBBI 50D Receptacle, Vertical, 68 Circuits

Documents:
[3D Model](#) [Product Specification PS-71660-001 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification
CSA LR19980
UL E29179


General
Product Family PCB Receptacles
Series 71660
Application Board-to-Board, Signal
Overview EBBI 50D Connector System
Product Name EBBI
UPC 800753756342

Physical
Circuits (Loaded) 68
Circuits (maximum) 68
Color - Resin Black
Durability (mating cycles max) 2000
Flammability 94V-0
Glow-Wire Capable No
Guide to Mating Part Yes
Material - Metal Phosphor Bronze
Material - Plating Mating Gold
Material - Plating Termination Tin
Material - Resin High Temperature Thermoplastic
Net Weight 3.963/g
Number of Rows 2
Orientation Vertical
PC Tail Length 3.40mm
PCB Locator Yes
PCB Retention Yes
PCB Thickness - Recommended 1.57mm
Packaging Type Tray
Pitch - Mating Interface 1.27mm
Plating min - Mating 0.762µm
Plating min - Termination 0.254µm
Polarized to PCB Yes
Temperature Range - Operating -40° to +105°C
Termination Interface: Style Through Hole

Electrical
Current - Maximum per Contact 1.0A
Voltage - Maximum 30V

Solder Process Data
Lead-freeProcess Capability SMC&WAVE
Process Temperature max. C 260

Material Info
Engineering Number A-71660-1068



Series image - Reference only

EU ELV
Not Relevant

EU RoHS **China RoHS**
Compliant
REACH SVHC
Not Contained Per -
ED/61/2018 (27 June
2018)
Halogen-Free
Status
Low-Halogen
For more information, please visit [Contact US](#)

China ROHS Green Image
ELV Not Relevant
RoHS Phthalates Not Contained

Search Parts in this Series
71660 Series

Mates With
71661

Reference - Drawing Numbers

Product Specification

Sales Drawing

PS-71660-001

SDA-71660-1***, SDA-71660-1****

This document was generated on 10/05/2018

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION