


**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1805600001](#)  
**Status:** **Active**  
**Overview:** [LED Array Holders, Dual-Ended Wire Trap](#)  
**Description:** [LED Array Holder for 15.85 by 15.85mm COB, Rectangular Version, Gold \(Au\) Plating](#)

**Documents:**

<a href="#">3D Model</a>	<a href="#">Application Specification AS-180328-001-001 (PDF)</a>
<a href="#">Drawing (PDF)</a>	<a href="#">Packaging Specification PK-180560-001-000 (PDF)</a>
<a href="#">Product Specification PS-180560-001-001 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>
<a href="#">Product Specification TS-180155-001-001 (PDF)</a>	



**Agency Certification**

UL E345583

**General**

Product Family	Solid State Lighting
Series	<a href="#">180560</a>
Array Type	Cree
Beam Angle	N/A
Height	4.10mm
Overview	<a href="#">LED Array Holders, Dual-Ended Wire Trap</a>
Product Name	Wire Trap Holder
Type	LED COB Array Holder
UPC	887191246482

**Physical**

Base Type	N/A
Color Rendering Index (CRI)	N/A
Correlated Color Temp (CCT)	N/A
Lamp Type	N/A
Mounting Style	Screws
Net Weight	3.873/g
Packaging Type	Tray

**Electrical**

Lamp Wattage - Maximum	N/A
Lumens	N/A
Voltage (Fixture) - Maximum	300V DC
Wiring Style	Poke In Wire Traps

**Material Info**

**Reference - Drawing Numbers**

Application Specification	AS-180328-001-001
Packaging Specification	PK-180560-001-000
Product Specification	PS-180560-001-001, TS-180155-001-001
Sales Drawing	SD-180560-001

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
ED/61/2018 (27 June  
2018)

**Halogen-Free**

**Status**

**Not Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[180560 Series](#)