

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0190670003](#)
Status: **Active**
Overview: [Solderless Terminals](#)
Description: NylaKrimp Funnel Entry Ring Tongue Terminal for 8 AWG Wire, Stud Size 8 (M4)

Documents:
[3D Model](#) [Product Specification PS-19902-013-001 \(PDF\)](#)
[Drawing \(PDF\)](#) [Product Specification PS-19902-016-001 \(PDF\)](#)
[Product Specification PS-19902-011-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification
CSA LR18689
UL E32244


General
Product Family Ring and Spade Terminals
Series [19067](#)
Crimp Quality Equipment Yes
Mil-Spec N/A
Overview [Solderless Terminals](#)
Product Name NylaKrimp
Type Ring
UPC 800753065222

Physical
Barrel Type Closed - Brazed
Flammability 94V-2
Insulation Nylon (PA)
Material - Plating Mating Tin
Net Weight 3.520/g
Packaging Type Bag
Plating min - Mating 2.540µm
Plating min - Termination 2.540µm
Stud Size 8 (M4)
Termination Interface: Style Crimp or Compression
Wire Insulation Diameter 8.98mm max.
Wire Size AWG 8

Solder Process Data
Lead-freeProcess Capability N/A

Material Info
Engineering Number D-950-08

Reference - Drawing Numbers
Product Specification PS-19902-011-001, PS-19902-013-001,
PS-19902-016-001
Sales Drawing SD-19067-017



Series image - Reference only

EU ELV
Not Relevant

EU RoHS **China RoHS**
Compliant
REACH SVHC
Not Contained Per -
ED/61/2018 (27 June
2018)
Halogen-Free
Status
Not Low-Halogen

**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any
non-product compliance questions.

China ROHS	Green Image
ELV	Not Relevant
Prop65	Compliant
RoHS Phthalates	Not Contained

Search Parts in this Series
[19067](#) Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION