

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0191990007](#)
Status: **Active**
Overview: [Splices](#)
Description: Butt - Window Splice for 18-22 AWG Wire

Documents:

Drawing (PDF)	Product Specification PS-19902-013-001 (PDF)
Product Specification PS-19902-011-001 (PDF)	RoHS Certificate of Compliance (PDF)

General

Product Family	Splices
Series	19199
Crimp Quality Equipment	Yes
Mil-Spec	N/A
Overview	Splices
Product Name	Butt - Window
UPC	800753046801

Physical

Barrel Type	Closed
Color - Resin	Red
Insulation	Nylon (PA)
Material - Metal	Copper
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	1.203/g
Packaging Type	Bag
Temperature Range - Operating	-55° to +105°C
Wire Insulation Diameter	3.56mm max.
Wire Size AWG	18, 20, 22
Wire Size mm ²	0.35-0.80

Electrical


Voltage - Maximum	300V
-------------------	------

Material Info

Engineering Number	WA-840
--------------------	--------

Reference - Drawing Numbers

Product Specification	PS-19902-011-001, PS-19902-013-001
Sales Drawing	SD-19199-003



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/61/2018 (27 June
2018)

Halogen-Free

Status

Low-Halogen

**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any
non-product compliance questions.

China ROHS	Green Image
ELV	Not Relevant
Prop65	Compliant
RoHS Phthalates	Not Contained

Search Parts in this Series

[19199 Series](#)