

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0192760005

Status:

Active

Overview:

Quixon Terminals

Description:

Quixon Quick Disconnect, InsulKrimp Style, Female, Fully Insulated Blue, 14-16 AWG, Loose



Series image - Reference only

Documents:

- [3D Model](#)
- [Drawing \(PDF\)](#)
- [Product Specification PS-19902-011-001 \(PDF\)](#)
- [Product Specification PS-19902-013-001 \(PDF\)](#)
- [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA

LR18689

UL

E79133

General

Product Family

Quick Disconnects

Series

19276

Comments

Low Insertion Force

Crimp Quality Equipment

Yes

Insulated

Fully

Overview

Quixon Terminals

Product Name

InsulKrimp, Quixon

Type

Quick Disconnect

UPC

884982565111

Physical

Barrel Type

Closed

Color - Resin

Blue

Flammability

94V-2

Gender

Female

Glow-Wire Capable

No

Insulation

Nylon (PA)

Lock to Mating Part

None

Material - Metal

Brass

Material - Plating Mating

Tin

Material - Plating Termination

Tin

Net Weight

0.943/g

Orientation

Straight

Packaging Type

Bag

Tab Thickness

0.41mm

Tab Width

7.87mm

Temperature Range - Operating

-55° to +105°C

Wire Insulation Diameter

4.06mm

Wire Size AWG

14, 16

Electrical

Voltage - Maximum

600V

Material Info

Engineering Number

BB-2206-LIF

Reference - Drawing Numbers

Product Specification

PS-19902-011-001, PS-19902-013-001

Sales Drawing

SD-19276-001

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
ED/61/2018 (27 June
2018)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

19276 Series

This document was generated on 10/12/2018

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION