

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0194170024](#)
Status: **Active**
Overview: [MX150L Industrial Sealed Connector System](#)
Description: MX150L Male Terminal for 18-22 AWG Wire, Metal Strip Carrier, Length 25.40mm

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-19417-001-001 \(PDF\)](#) [Product Literature \(PDF\)](#)

Agency Certification

CSA LR18689
 UL E152602

General

Product Family Crimp Terminals
 Series [19417](#)
 Application Power, Wire-to-Wire
 Comments UL E152602|Standard Length
 Crimp Quality Equipment Yes
 Overview [MX150L Industrial Sealed Connector System](#)
 Packaging Alternative [19417-0048 \(Loose\)](#)
 Product Literature Order No 987650-2181
 Product Name MX150L
 UPC 756054795569


Physical

Durability (mating cycles max) 25
 Gender Male
 Material - Metal High Performance Alloy (HPA)
 Material - Plating Mating Tin
 Material - Plating Termination Tin
 Net Weight 0.347/g
 Packaging Type Reel
 Plating min - Mating 1.905µm
 Plating min - Termination 1.905µm
 Termination Interface: Style Crimp or Compression
 Wire Insulation Diameter 2.36-2.74mm
 Wire Size AWG 18, 20, 22
 Wire Size mm² N/A

Material Info

Reference - Drawing Numbers

Product Specification PS-19417-001-001
 Sales Drawing SD-19417-001



Series image - Reference only

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
 ED/61/2018 (27 June
 2018)

Halogen-Free

Status

Low-Halogen

**Need more information on product
 environmental compliance?**

Email productcompliance@molex.com
 Please visit the [Contact Us](#) section for any
 non-product compliance questions.

China ROHS	Green Image
ELV	Compliant
Prop65	Compliant
RoHS Phthalates	Not Contained

Search Parts in this Series

[19417 Series](#)

Mates With

[19420](#)

Use With

[19419](#) , [19429](#)