

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0194190015
Status: Active
Overview: MX150L Industrial Sealed Connector System
Description: MX150L 10 Circuit Plug for 18-22 AWG Wire



Documents:	
3D Model	Packaging Specification PK-19419-001 (PDF)
Drawing (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification PS-19417-001-001 (PDF)	Product Literature (PDF)
Application Specification AS-19417-001-001 (PDF)	
Agency Certification	
CSA	LR18689
UL	E152602
General	
Product Family	Crimp Housings
Series	19419
Application	Power, Wire-to-Wire
Comments	IP67 rated; conforms to UL 1977. NOT suitable for automotive applications with requirements such as USCAR-2, USCAR-25, GMW3191, AK Testing, J2030, Volvo Technology Requirements, and Toyota Connector Spec (TCS)
Overview	MX150L Industrial Sealed Connector System
Product Literature Order No	987650-2181
Product Name	MX150L
UPC	822348020010
Physical	
Circuits (maximum)	10
Flammability	94V-0
Gender	Plug
Glow-Wire Capable	No
Lock to Mating Part	Yes
Net Weight	21.958/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	5.84mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +125°C
Electrical	
Current - Maximum per Contact	18.0A
Material Info	
Reference - Drawing Numbers	
Application Specification	AS-19417-001-001
Packaging Specification	PK-19419-001
Product Specification	PS-19417-001-001
Sales Drawing	SD-19419-005

EU ELV Not Relevant	
EU RoHS Compliant REACH SVHC Not Contained Per - ED/108/2014 (17 Dec 2014) Halogen-Free Status Low-Halogen Need more information on product environmental compliance? Email productcompliance@molex.com Please visit the Contact Us section for any non-product compliance questions.	China RoHS China ROHS ELV RoHS Phthalates
	Green Image Not Relevant Not Reviewed

Search Parts in this Series 19419 Series
Mates With 19418 Receptacle Assemblies
Use With 19417 Male Crimp Terminals

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION