

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0430610012](#)
Status: **Active**
Overview: [SPOX Connector System](#)
Description: 3.96mm Pitch SPOX Housing, 12 Circuits, Natural

Documents:

[3D Model](#) [Packaging Specification PK-43061-001-001 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR19980
 UL E29179

General

Product Family Crimp Housings
 Series [43061](#)
 Application Power, Wire-to-Board
 Overview [SPOX Connector System](#)
 Product Name SPOX
 UPC 800753617131

Physical

Breakaway No
 Circuits (maximum) 12
 Circuits Detail 12
 Color - Resin Natural
 Flammability 94V-0
 Gender Receptacle
 Glow-Wire Capable No
 Keying to Mating Part None
 Lock to Mating Part Yes
 Material - Resin Polyester
 Net Weight 3.933/g
 Number of Rows 1
 Packaging Type Bag
 Panel Mount No
 Pitch - Mating Interface 3.96mm
 Pitch - Termination Interface 3.96mm
 Polarized to Mating Part Yes
 Stackable No
 Temperature Range - Operating 0° to +75°C


Solder Process Data

Lead-freeProcess Capability N/A

Material Info

Reference - Drawing Numbers

Packaging Specification PK-43061-001-001
 Sales Drawing SD-43061



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
 ED/61/2018 (27 June
 2018)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[43061 Series](#)

Mates With

3.96mm Pitch KK or SPOX headers

Use With

SPOX Terminal [5194](#) , [5225](#)