

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0444411002](#)
Status: **Active**
Overview: [Sabre Power Connector](#)
Description: 7.50mm Pitch Sabre Receptacle Crimp Housing, UL 94V-2, 2 Circuits, Natural

Documents:

3D Model	Packaging Specification PK-44441-001-001 (PDF)
Drawing (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification PS-44441-9999-001 (PDF)	Product Literature (PDF)

Agency Certification

UL E29179

General

Product Family	Crimp Housings
Series	44441
Application	Power, Wire-to-Board, Wire-to-Wire
Comments	Positive mating lock and integrated Terminal Position Assurance (TPA) standard.
Overview	Sabre Power Connector
Product Literature Order No	987650-5662
Product Name	Sabre
UPC	822348670574

Physical

Circuits (maximum)	2
Color - Resin	Natural
Flammability	94V-2
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	1.852/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	7.50mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +75°C

Electrical

Current - Maximum per Contact 18.0A

Solder Process Data

Lead-freeProcess Capability N/A

Material Info

Reference - Drawing Numbers

Packaging Specification	PK-44441-001-001
Product Specification	PS-44441-9999-001
Sales Drawing	444410000-SD-000



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - ED/61/2018 (27 June 2018)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[44441 Series](#)

Mates With

Plug Housing [43680-1002](#), 2 Circuit, UL 94V-2 Vertical or Right Angle Headers [43160](#), 2 Circuit, UL 94V-2 Right Angle, UL1977 finger proof compliant [46007](#)

Use With

Female Crimp Terminals [43375](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION