

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0500138100](#)
Status: **Active**
Description: 2.00mm Pitch Crimp Terminal, for 51005 Housing

Documents:

[3D Model](#) [Packaging Specification SPK-50013-001-001 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-51005-001-001 \(PDF\)](#)

General

Product Family Crimp Terminals
Series [50013](#)
Application Signal
Crimp Quality Equipment Yes
Packaging Alternative [50013-8000](#) (Reel)
Product Name N/A
UPC 800753576254

Physical

Gender Female
Material - Metal Phosphor Bronze
Material - Plating Mating Tin
Material - Plating Termination Tin
Net Weight 47.900/mg
Packaging Type Bag
Plating min - Mating 0.889µm
Plating min - Termination 0.914µm
Termination Interface: Style Crimp or Compression
Wire Insulation Diameter 0.90-1.15mm
Wire Size AWG 24, 26, 28
Wire Size mm² N/A


Electrical

Current - Maximum per Contact 2.0A
Voltage - Maximum 125V

Material Info

Reference - Drawing Numbers

Crimp Specification CS-50012_50013
Packaging Specification SPK-50013-001-001
Product Specification PS-51005-001-001
Sales Drawing SD-50013-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
ED/61/2018 (27 June
2018)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

[50013](#) Series

Mates With

[50012](#)

Use With

[51005](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION