

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0006660012

Status:

Active

Overview:

Pre-Crimped Leads

Description:

Pre-Crimped Lead PicoBlade Female-to-PicoBlade Female, 152.00mm, 28 AWG



Documents:	
Drawing (PDF)	RoHS Certificate of Compliance (PDF)
General	
Product Family	Cable Assemblies
Series	666
Assembly Configuration	Pre-crimped Lead Only
Connector to Connector	PicoBlade Crimp Terminals
Overview	Pre-Crimped Leads
Product Name	PicoBlade
UPC	800754232906
Physical	
Cable Length	152.00mm
Circuits (Loaded)	1
Color - Resin	Red
Gender	Female
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	25.430/g
Packaging Type	Bag
Single Ended	No
Wire Size AWG	28
Wire/Cable Type	Discrete Wire
Material Info	
Reference - Drawing Numbers	
Sales Drawing	SD-66600-012

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per	
-ED/01/2018 (15	
January 2018)	
Halogen-Free	
Status	
Not Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

666 Series

Mates With

50125 Crimp Terminal, 50133 Crimp Terminal

Use With

PicoBlade Housings 51021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION