

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0795763005](#)  
**Status:** **Active**  
**Overview:** [iPass Connector System](#)  
**Description:** Mini Multi-Lane iPass-to-(4) x 1 SATA, 36 Circuits, 28 AWG, 1.0m Length, iPass-to-Controller, Pinout 2

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family	Cable Assemblies
Series	<a href="#">79576</a>
Assembly Configuration	Dual Ended Connectors
Connector to Connector	Serial ATA-to-iPass
Overview	<a href="#">iPass Connector System</a>
Product Name	iPass, Mini Multi-Lane, PCI Express, SAS, Serial ATA
UPC	822350128988

**Physical**

Cable Length	1.0m
Circuits (Loaded)	36
Color - Resin	Black, Natural
Gender	Male-Male
Lock to Mating Part	Yes
Material - Metal	Phosphor Bronze
Material - Resin	Low Density Polyethylene, Polyester
Net Weight	82.070/g
Packaging Type	Bag
Pitch - Mating Interface	0.80mm
Single Ended	No
Termination Interface: Style	Crimp or Compression, Surface Mount
Wire Insulation Diameter	N/A
Wire Size AWG	28
Wire/Cable Type	Twinax


**Electrical**

Current - Maximum per Contact	1.0A
Shielded	Yes
Voltage - Maximum	30V AC

**Solder Process Data**

Lead-freeProcess Capability	N/A
-----------------------------	-----

**Material Info**



**EU ELV**

**Compliant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Contained Per -  
ED/01/2018 (15  
January 2018)  
2,4-Di-tert-butyl-6-(5-  
chlorobenzotriazol-2-  
yl)p

**Halogen-Free**

**Status**

**Not Low-Halogen**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Green Image
ELV	Compliant
RoHS Phthalates	Not Contained

**Search Parts in this Series**

[79576](#) Series

**Mates With**

[75783](#) iPass Right Angle Connector. [75784](#) iPass Vertical Connector