

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0873810864

Status:

Active

Overview:

Milli-Grid Connector System

Description:

2.00mm Pitch Milli-Grid Receptacle, Surface Mount, Top Entry, 0.38µm Gold (Au) Plating, with Cover, without Locating Pegs, 8 Circuits, Lead-Free

Documents:

3D Model

Drawing (PDF)

Product Specification PS-87380-002-001 (PDF)

Packaging Specification 873810001-PK-000 (PDF)

RoHS Certificate of Compliance (PDF)

Product Literature (PDF)

Agency Certification

CSA

LR19980

UL

E29179

General

Product Family

PCB Receptacles

Series

87381

Application

Board-to-Board, Signal

Comments

With Cover

Overview

Milli-Grid Connector System

Product Literature Order No

987650-1991

Product Name

Milli-Grid

UPC

822348482719

Physical

Circuits (Loaded)

8

Circuits (maximum)

8

Color - Resin

Black

Durability (mating cycles max)

25

Flammability

94V-0

Glow-Wire Capable

No

Lock to Mating Part

None

Material - Metal

Phosphor Bronze

Material - Plating Mating

Gold

Material - Plating Termination

Tin

Material - Resin

High Temperature Thermoplastic

Net Weight

0.175/g

Number of Rows

2

Orientation

Vertical

PCB Locator

No

PCB Retention

None

Packaging Type

Tube

Pitch - Mating Interface

2.00mm

Pitch - Termination Interface

2.00mm

Plating min - Mating

0.381µm

Plating min - Termination

1.270µm

Polarized to PCB

No

Robotic Placement

Pick and Place Cap

Stackable

Yes

Surface Mount Compatible (SMC)

N/A

Temperature Range - Operating

-55° to +105°C

Termination Interface: Style

Surface Mount

Electrical

Current - Maximum per Contact

1.9A

Voltage - Maximum

125V



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
ED/61/2018 (27 June
2018)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

87381 Series

Mates With

87758 Vertical, Through Hole, Stackable PCB Header, 87759 Vertical, Surface Mount, Stackable PCB Header, 87760 Right Angle, Through Hole, Stackable PCB Header, 87831 Vertical, Through Hole PCB Header, 87832 Vertical, Surface Mount PCB

Solder Process Data

Duration at Max. Process Temperature (seconds)	012
Lead-freeProcess Capability	REFLOW
Max. Cycles at Max. Process Temperature	001
Process Temperature max. C	260

Material Info

Reference - Drawing Numbers

Packaging Specification	873810001-PK-000
Product Specification	PS-87380-002-001
Sales Drawing	SD-87381-**6*, SD-87381-XX6X-001

This document was generated on 10/23/2018

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION