



3W

VT-503 3W LED EMERGENCY DOWNLIGHT COLORCODE:5500K

Lumens
140

Dimensions
38.5x22x25mm

White
 SKU:8274

2 YEARS
 WARRANTY



Technical Information

Watts:	3	Body Type:	Poly Carbonate & Aluminium
Lumens:	140	IP Rating:	IP20
Battery Charging Current:	90mA	Dimmable:	No
Battery Discharging Current:	300mA	Warranty (Years):	2
Battery Type:	3.6V 1800mAh Ni-cd Battery	Operation Temperature:	-25 to +50°C
Emergency Operation Time:	3 Hours	Input Power:	AC:220-240V, 50/60Hz
Unit Color:	White		

Features

- ✓ Efficient thermal management technology.
- ✓ High performance Ni-Cd batteries made for Longevity & low maintenance.
- ✓ LEDs mounted on print circuit board.
- ✓ Low energy consumption only 2.0 watts at 120V.
- ✓ Thermoplastic PC housing, Rectangular type plastic with different signs.
- ✓ Single or double face configuration.
- ✓ Reliable Emergency backup of 3 hours.
- ✓ Universal (wall, side or ceiling) mounting.
- ✓ LED indicator light and push button test switch.

Packaging

Unit Details

Gross Weight(GW) Kgs	0.33
Unit CBM	0

Listing Details

EAN Code	3800157627269
Commodity Code	9405403990

Master Box Packaging

Master Box Qty (Pcs Per Carton)	20
---------------------------------	----

READY STOCKS IN
UK & EU



Dispatch within
24 Hours

www.vtacexports.com

OUR PRODUCTS ARE
CURRENTLY SOLD IN OVER
70
COUNTRIES