



15W

VT-15 15W FULL ROUND DOME LIGHT WITH SAMSUNG CHIP
 COLORCODE:4000K IP65

Lumens 1400	Beam Angle 120	Dimensions Ø320x100mm
-----------------------	--------------------------	---------------------------------

Day White
 SKU:801



Technical Information

Watts:	15	IP Rating:	IP65
Lumens:	1400	Dimmable:	No
Shape:	Round	Warranty (Years):	5
Beam Angle:	120	CRI:	>80
Unit Color:	White	Operation Temperature:	-20°C to +45°C
Body Type:	PC	Input Power:	AC:200-240V,50/60Hz
Long life:	30,000 Hours	Sensor Compatibility:	Yes
LED Chip Type:	SMD-Samsung Chip		

Features

- ✓ Premium quality LEDs with reliable lifetime.
- ✓ Efficient thermal management technology.
- ✓ 100% PC for Endurance/Durability.
- ✓ Maintained operation-suitable for long working hours.
- ✓ Corrosion free mounting clamps.
- ✓ Range of Dome Lights for Elegance,Ambience,Utility,Security,Weatherproof.
- ✓ Constant current LED Driver for Instant start and consistent operation.
- ✓ Applications - Office, Art Gallery, Display Case, Accent Lighting etc



Note: Suitable & Recommended for maximum daily use of 10-12 hours, usage beyond this would void the warranty

Packaging

Unit Details

Gross Weight(GW) Kgs	1.2
Unit CBM	0.011979

Listing Details

EAN Code	3800157636469
Commodity Code	9405403990

Master Box Packaging

Master Box Qty (Pcs Per Carton)	10
Qty Per Pallet	100

READY STOCKS IN
UK & EU



Dispatch within
24 Hours

www.vtacexports.com

OUR PRODUCTS ARE
CURRENTLY SOLD IN OVER
70
COUNTRIES