

Motor No.: ZH417-17-04-RO

WINDING REVISION A	ECN#	0
FULL STEP ANGLE		0.9°
MOTOR FRAME SIZE	NEMA Size	17
BODY LENGTH		1.7" Maximum
RATED CURRENT/PHASE		0.7Amps
RESISTANCE/PHASE		13.75 Ω ±10%
INDUCTANCE/PH		5.69mH±20%
ROTOR INERTIA		0.14oz-in ²
BEARING TYPE		ABEC3
NOMINAL HOLDING TORQUE 2 PHASE ON (±10%)		33.5 oz-in
AMBIENT OPERATING TEMPERATURE		-20° C to 50° C
AMBIENT OPERATING HUMIDITY(non condensing)		85% Max
LEAD WIRES		(4) # 26 AWG PVC
DIELECTRIC STRENGTH		500V
SPECIAL SPECIFICATIONS:		

LEAD WIRE CONNECTION

- A RED
- \bar{A} BLUE
- B GREEN
- \bar{B} BLACK

Switching Sequence					
CCW	STEP	A	\bar{A}	B	\bar{B}
↓	1	+	-	+	-
	2	+	-	-	+
	3	-	+	-	+
	4	-	+	+	-
	1	+	-	+	-

Motor Rotation Viewed from Front Shaft End

Printed 10/10/2018 1:23:02 PM