

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1110150100](#)  
**Status:** **Active**  
**Overview:** [HSAutoLink Interconnect Systems](#)  
**Description:** HSAutoLink Cable Assembly, USCAR/USB TYPE A Receptacle-to-MINI-B Plug, 0.50m Length, Polarization A

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)  
[Product Specification PS-68800-001-001 \(PDF\)](#)

**General**

Product Family	Cable Assemblies
Series	<a href="#">111015</a>
Assembly Configuration	Dual Ended Connectors
Comments	USCAR-30 Compliant
Connector to Connector	USB Type A-to-Mini-B
Overview	<a href="#">HSAutoLink Interconnect Systems</a>
Product Name	HSAutoLink USCAR/USB
UPC	883906510060


**Physical**

Cable Length	0.50m
Circuits (Loaded)	N/A
Gender	Male-Female
Lock to Mating Part	Yes
Net Weight	38.730/g
Packaging Type	Bag
Single Ended	No
Wire/Cable Type	Round

**Material Info**

**Reference - Drawing Numbers**

Product Specification	PS-68800-001-001
Sales Drawing	SD-111015-006



**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per  
-ED/01/2018 (15  
January 2018)

**Halogen-Free**

**Status**

**Not Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[111015 Series](#)

**Mates With**

[49616 USCAR/USB Header](#)