


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0194170011](#)
Status: **Active**
Overview: [MX150L Industrial Sealed Connector System](#)
Description: MX150L Male Terminal for 14-16 AWG Wire, Metal Strip Carrier, Length 25.40mm



Series image - Reference only

Documents:

Drawing (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification PS-19417-001-001 (PDF)	Product Literature (PDF)

Agency Certification

CSA	LR18689
UL	E152602

General

Product Family	Crimp Terminals
Series	19417
Application	Power, Wire-to-Wire
Comments	UL E152602 Standard Length
Crimp Quality Equipment	Yes
Overview	MX150L Industrial Sealed Connector System
Packaging Alternative	19417-0047 (Loose)
Product Literature Order No	987650-2181
Product Name	MX150L
UPC	756054792087

Physical

Durability (mating cycles max)	25
Gender	Male
Material - Metal	High Performance Alloy (HPA)
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.392/g
Packaging Type	Reel
Plating min - Mating	1.905µm
Plating min - Termination	1.905µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	2.87 -3.53mm
Wire Size AWG	14, 16
Wire Size mm²	N/A

Material Info

Reference - Drawing Numbers

Product Specification	PS-19417-001-001
Sales Drawing	SD-19417-001

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
ED/61/2018 (27 June
2018)

Halogen-Free

Status

Low-Halogen

**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any
non-product compliance questions.

China ROHS	Green Image
ELV	Not Relevant
Prop65	Compliant
RoHS Phthalates	Not Contained

Search Parts in this Series

[19417](#) Series

Mates With

[19420](#)

Use With

[19419](#) , [19429](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION