

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0022051122

Status:


Active

Overview:

Mini-Latch Wire-to-Board System

Description:

Mini-Latch / KK Wire-to-Board Header, Right-Angle, Friction Lock, 12 Circuits, Tin (Sn) Plating



Documents:	
3D Model	Product Specification PS-51191-002 (PDF)
Drawing (PDF)	Application Specification 511910000-AS-000 (PDF)
Product Specification PS-5046-002-001 (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification	
UL	E29179
General	
Product Family	PCB Headers
Series	5046
Application	Signal, Wire-to-Board
Overview	Mini-Latch Wire-to-Board System
Product Name	KK, Mini-Latch
UPC	800753740211
Physical	
Breakaway	No
Circuits (Loaded)	12
Circuits (maximum)	12
Durability (mating cycles max)	30
First Mate / Last Break	No
Flammability	94V-0
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Nylon
Net Weight	1555.200/mg
Number of Rows	1
Orientation	Right Angle
PC Tail Length	3.40mm
PCB Locator	No
PCB Retention	None
PCB Thickness - Recommended	1.60mm
Packaging Type	Bag
Pitch - Mating Interface	2.50mm
Pitch - Termination Interface	2.50mm
Plating min - Mating	5.080µm
Plating min - Termination	5.080µm
Polarized to PCB	No
Shrouded	Partial
Stackable	No
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	-40° to +105°C
Termination Interface: Style	Through Hole
Electrical	

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Contained Per - ED/61/2018 (27 June 2018)	
Dodecachloropentacyclo[12.2.1.16,9.02,13.05,10]o	
Halogen-Free	
Status	
Not Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

5046 Series

Mates With

2.50mm Pitch Housing 51191

Current - Maximum per Contact	3.0A
Voltage - Maximum	250V
Material Info	
Engineering Number	5046-12A
Reference - Drawing Numbers	
Application Specification	511910000-AS-000
Product Specification	PS-5046-002-001, PS-51191-002
Sales Drawing	SD-5046-NA

This document was generated on 10/18/2018

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION